

2-326875-1 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

[View 3D PDF](#)

Ring and Spade Tongue Terminals

TERMINAL,PIDG R 26-22 6

2-326875-1

TE Internal Number: 2-326875-1

Product Highlights [View All](#)

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Body Style = PIDG
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#)

[Features](#)

[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

| Product Type Features | | Body Features | |
|-------------------------------------|--------------------|-----------------------------------|------------------------------------|
| Receptacle Style | Straight | Body Style | PIDG |
| Barrel Type | Closed Barrel | Wire Range (mm [AWG]) | 0.12-0.40 ² [26-22] |
| Wire/Cable Type | Regular Wire | Material | Copper |
| Insulation | Yes | Insulation Material | Nylon |
| Insulation Support | Insulation Support | Contact Features | |
| Stud Size | 6 [M3.5] | Terminal Shape | Ring Tongue |
| Shape | RING-041 | Class | 2 |
| Heavy Duty | No | Industry Standards | |
| Finish | Tin | Government/Industry Qualification | Yes |
| Color | Yellow | Government/Industry Part Number | MS25036-145 |
| Electrical Characteristics | | RoHS/ELV Compliance | RoHS compliant, ELV compliant |
| Voltage (VAC) | 300 | Lead Free Solder Processes | Not relevant for lead free process |
| Termination Features | | RoHS/ELV Compliance History | Always was RoHS compliant |
| Wire/Cable Size (CMA) | 202 - 810 | Packaging Features | |
| Dimensions | | Packaging Method | Tape Mounted |
| Insulation Diameter (mm [in]) | 2.08 [.082] Max. | Other | |
| Stud Diameter (mm [in]) | 3.51 [0.138] | Brand | AMP |
| Tongue Material Thickness (mm [in]) | 0.50 [0.0197] | | |

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

