


1746817-1 Product Details

[Share](#) [Print](#) [Email](#)



1746817-1

TE Internal Number: 1746817-1
Active

[View 3D PDF](#)

0.025 Series and Hybrid Connectors and Contacts

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Product Series = 0.64/2.3 II
- Wire-to-Wire
- Accessory
- Accessory Type = Wire Cover
- 60 Positions

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [SEALED EFI ECU 0.64/2.3II I/O CONNECTOR \(1\) \(PDF, Japanese\)](#)
- [SEALED EFI ECU 0.64/2.3II I/O CONNECTOR \(2\) \(PDF, Japanese\)](#)

Application Specifications:

- None Available

Instruction Sheets:

- [SEALED EFI ECU 0.64/2.3II I/O CONNECTOR \(1\) \(PDF, Japanese\)](#)
- [SEALED EFI ECU 0.64/2.3II I/O CONNECTOR \(2\) \(PDF, Japanese\)](#)

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version F\)](#)
- [3D Model \(IGES, Version F\)](#)
- [3D Model \(STEP, Version F\)](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Series = 0.64/2.3 II
- Product Type = Accessory
- Accessory Type = Wire Cover
- Accessory Color = Black
- Strain Relief = Without
- Sealed = No

Mechanical Attachment:

- Panel Mount Retention = Without

Dimensions:

- Length (X-Axis) (mm[in]) = 61.96 [2.4394]
- Width (Z-Axis) (mm[in]) = 28.10 [1.1063]
- Profile Height (Y-Axis) (mm[in]) = 51.70 [2.035]

Contact Features:

- Shunts/Shorting Bars = Without

Housing Features:

- Housing Material = PBT

Configuration Features:

- Number of Positions = 60
- GET 0.64 Connector System = No

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- For Use With = Plug: 1612283 or 1747140

Operation/Application:

- Application Use = Wire-to-Wire

Packaging Features:

- Packaging Method = Paper Box, Plastic Bag
- Packaging Quantity = 300

Other:

- Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

