

1838240 -3 Product Details

 **Live Product Chat** US Only
8:30am - 5pm ET, Mon - Fri



1838240 -3

 [Active](#)

M8/M12 Connector System

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Lead Assembly
- ? Lead Assembly Type = Cable
- ? Wire Size = 0.34 (22 AWG) mm² [AWG]
- ? Number of Positions = 5
- ? Cable Length = 5.00 M

[View all Features](#) | [Find Similar Products](#)

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [M12 STRAIGHT MALE CONNECTOR 5 POSITION, PVC CABLE](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version C)
- ? [3D Model](#) (IGES, Version C)
- ? [3D Model](#) (STEP, Version C)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Lead Assembly
- ? [Wire Size \(mm² \[AWG\]\)](#) = 0.34 (22 AWG)
- ? [Number of Positions](#) = 5
- ? Insulation Material = PVC
- ? Shielded = No
- ? Thread Size = M12
- ? Gender = Male
- ? Mount Angle = Straight

Mechanical Attachment:

- ? Panel Mount = No

Body Related Features:

- ? [Lead Assembly Type](#) = Cable
- ? [Cable Length \(M \[ft\]\)](#) = 5.00 [16.404]
- ? Cable Color = Black
- ? Connector Color = Black
- ? Wire Color = Brown, White, Blue, Black, Green
- ? [LED](#) = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? Packaging Quantity = 20

Other:

- ? Brand = Tyco Electronics