



2111021-1 Product Details

Share Print Email



2111021-1

TE Internal Number: 2111021-1

Active

View 3D PDF

Work Area Outlets

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Region = Asia, Latin America, North America
- Faceplate
- 110 Connect Series, SL Series Series
- 1 Ports
- Unloaded Configuration

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [FACEPLATE KIT, NON-LABELED, SINGLE GANG, 1 PORT \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- [AMP NETCONNECT Single Gang and Double Gang Faceplate... \(PDF, English\)](#)

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version A\)](#)
- [3D Model \(IGES, Version A\)](#)
- [3D Model \(STEP, Version A\)](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Faceplate
- Series = 110 Connect, SL Series
- Grade = Residential
- Orientation = Vertical
- Color = Light Almond

Body Features:

- Port Style = Straight
- Capacity = 1-Gang

Configuration Features:

- Number of Ports = 1
- Configuration = Unloaded

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Identification Marking:

- Labeling Options = Label, Cover

Conditions for Usage:

- Accepts = 110Connect Shielded Modular Jacks, 110Connect Unshielded Modular Jacks, SL Series Multimedia Inserts, SL Series Multimedia Jacks, SL Series Shielded Modular Jacks, SL Series Unshielded Modular Jacks, XG Category 6 AMP-TWIST Modular Jacks

Operation/Application:

- Industry Application = NETCONNECT

Product Availability:

- Region = Asia, Latin America, North America

Other:

- Industry = Enterprise Network Solutions
- Brand = TE Connectivity

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

