

## 2198617-9 Product Details



2198617-9

TE Internal Number: 2198617-9

[Active](#)

### Cable Clamps

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Backshell/Cable Clamp
- Accessory Type = Cable Clamp
- Cable Clamp Type = Two-Piece RFI/EMI Shield
- 180° Cable Exit Angle
- Cable Insulation Diameter = 4.00 - 13.00 mm

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [LEAFLET, ASSEMBLY INSTRUCTIONS FOR ADK SERIES - \(PDF, English\)](#)
- [ADK SERIES DIE-CAST BACKSHELL, STRAIGHT ENTRY \(PDF, English\)](#)
- [ADK SERIES PLATED PLASTIC BACKSHELL STRAIGHT ENTRY \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Backshell/Cable Clamp
- Accessory Type = Cable Clamp
- [Cable Clamp Type](#) = Two-Piece RFI/EMI Shield
- [Shell Size](#) = 1
- [Screws and Retainer Clips](#) = With
- [Grommets](#) = With
- [Slide Latch](#) = Without
- Thread Size = 4-40

#### Electrical Characteristics:

- [Shielded](#) = Yes

#### Body Features:

- [Cable Exit Angle](#) = 180°
- [Cable Insulation Diameter \(mm \[in\]\)](#) = 4.00 - 13.00 [0.158 - 0.512]
- Number of Positions = 9
- Cable Clamp Material = ABS
- Shield Plating = Nickel

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Features:

- [Packaging Method](#) = Bulk

#### Other:

- Brand = AMP

#### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

#### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

#### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

