



Plug





RG/U	Part No.	Body Material and Finish	Center Contact Crimp			Ferrule Crimp	
			Military Tool	Positioner	Setting	Military Tool	Die Part No.
58, 58A, 58B, 58C	447647-1	Brass, Ni plated	M22520/2-01	M22520/2-20	6	M22520/5-01	M25520/5-11 A
142, 142A, 142B	447647-2	Brass, Ni plated	M22520/2-01	M22520/2-20	7	M22520/5-01	M22520/5-11 A
174, 174A, 188, 188A, 316	447647-3	Brass, Ni plated	M22520/2-01	M22520/2-20	4	M22520/5-01	M22520/5-35 B
174DB, 188DB, 316DB	447647-4	Brass, Ni plated	M22520/2-01	M22520/2-20	4	M22520/5-01	M22520/5-35 B
Belden YR20621 (RG58 Type)	447647-5	SST, passivated	M22520/2-01	M22520/2-20	6	M22520/5-01	M22520/5-11 A
174, 174A, 188, 188A, 316	447647-6	SST, passivated	M22520/2-01	M22520/2-20	4	M22520/5-01	M22520/5-35 B
142, 142A, 142B	447647-7	SST, passivated	M22520/2-01	M22520/2-20	7	M22520/5-01	M22520/5-11 A
174DB, 188DB, 316DB	447647-8	SST, passivated	M22520/2-01	M22520/2-20	4	M22520/5-01	M22520/5-35 B

Right Angle Plug



RG/U	Part No.	Body Material and Finish	Center Contact Crimp			Ferrule Crimp	
			Military Tool	Positioner	Setting	Military Tool	Die Part No.
58, 58A, 58B, 58C	447651-1	Brass, Ni plated	M22520/2-01	K997	6	M22520/5-01	M25520/5-11 A
142, 142A, 142B	447651-2	Brass, Ni plated	M22520/2-01	K997	7	M22520/5-01	M22520/5-11 A
174, 174A, 188, 188A, 316	447651-3	Brass, Ni plated	M22520/2-01	K997	4	M22520/5-01	M22520/5-35 B
174DB, 188DB, 316DB	447651-4	Brass, Ni plated	M22520/2-01	K997	4	M22520/5-01	M22520/5-35 B
Belden YR20621 (RG58 Type)	447651-5	SST, passivated	M22520/2-01	K997	6	M22520/5-01	M22520/5-11 A
174, 174A, 188, 188A, 316	447651-6	SST, passivated	M22520/2-01	K997	4	M22520/5-01	M22520/5-35 B
142, 142A, 142B	447651-7	SST, passivated	M22520/2-01	K997	7	M22520/5-01	M22520/5-11 A
174DB, 188DB, 316DB	447651-8	SST, passivated	M22520/2-01	K997	4	M22520/5-01	M22520/5-35 B

Bulkhead Jack



Recommended Panel Cutout

RG/U	Part No.	Body Material and Finish	Center Contact Crimp			Ferrule Crimp	
			Military Tool	Positioner	Setting	Military Tool	Die Part No.
142, 142A, 142B	448103-1	Brass, Ni plated	M22520/2-01	K997	7	M22520/5-01	M22520/5-11 A
174, 174A, 188, 188A, 316	448103-2	Brass, Ni plated	M22520/2-01	K997	4	M22520/5-01	M22520/5-35 B
Belden YR20621 (RG58 Type)	448103-3	SST, passivated	M22520/2-01	K997	6	M22520/5-01	M22520/5-11 A
174, 174A, 188, 188A, 316	448103-4	SST, passivated	M22520/2-01	K997	4	M22520/5-01	M22520/5-35 B