


5745018 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



5745018 -1

Active

Standard Cable Connectors

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Connector
- ? Product Series = HDJ -20
- ? Number of Positions = 9
- ? Plug
- ? Without Contacts

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(8\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [PLUG CONNECTOR, SIZE 1, 9 POS, AMPLIMITE HDP](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [AMPLIMITE* HDP -20 Subminiature D Connector With F Cr...](#) (PDF, English)

Application Specifications:

- ? [AMPLIMITE HDP -20 & Econo Crimp Snap Subminiature D C...](#) (PDF, English)

Instruction Sheets:

- ? [AMPLIMITE* Cord Guard Assemblies and AMPLIMITE 'Sque...](#) (PDF, English)
- ? [AMPLIMITE High Density \(HDP -20\) Connectors with Crim...](#) (PDF, English)
- ? [AMP* INSERTION/EXTRACTION TOOL 91285 -1 AND REPLACEME...](#) (PDF, English)

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version O)
- ? [3D Model](#) (IGES, Version O)
- ? [3D Model](#) (STEP, Version O)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)
- ? [Mating Products \(8\)](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Product Series](#) = HDJ -20
- ? Number of Positions = 9
- ? [Gender](#) = Plug
- ? [Mating Connector Lock](#) = Without
- ? [Shell Size](#) = 1
- ? [Shell Type](#) = Full Metal Shell
- ? [Grounding Indents](#) = Without
- ? Grade = Standard
- ? Color = Black
- ? Shell Material = Steel

Body Related Features:

- ? Shell Plating = Zinc
- ? Insert Material = Nylon
- ? Used With = Size 20 Crimp Snap -in Contacts

Contact Related Features:

- ? [Contacts](#) = Without

Housing Related Features:

- ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = AMP