

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	ECR-08-026821	10DEC2008	RPE	JO
	A	INITIAL ISSUE	12 SEP 05	MGR	DB

NOTES:

1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 874-1
 CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION

2 INDIVIDUAL LENGTH DIFFERENCE ON BOTH SIDES ≤ 50 mm

3 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH
 INDIVIDUALLY PACKED ASSEMBLY

4 DAT LABEL INFO:

- UNIQUE SERIAL NUMBER
- TYCO LOGO PN
- MANUFACTURING LOCN.

5 BLANK LABEL

6 CABLE INFO:

CORE DIA - 62,5/125 μ m

OUTER DIA - 2,5 x 5,0 mm

JACKET COLOR - ORANGE

JACKET MATERIAL - LSZH

STANDARD LENGTHS ACCORDING TO
 CUSTOMER DRAWING 1206850

PART NUMBER	"L" (Meter)
X-5349574-Y	XY,0
9-5349574-0	0,5
9-5349574-1	1,5
9-5349574-4	0,4
9-5349574-7	250,0
9-5349574-8	150,0
9-5349574-9	9,5
0-5349574-0	100,0
8-5349574-1	130,0
8-5349574-2	160,0
8-5349574-3	1000,0
8-5349574-4	90,0
8-5349574-5	100,0

Qty	Part Number	Description	Item
2	-	FOAC DAT-85 LABEL	6
4	-	KIT, MM, CER, ASSY, BULK	5
4	-	CRIMP EYELET, BRIGHT TIN	4
2	-	FOAC BOOT 2.5BAY, BLACK	3
2	-	FOAC BOOT 2.5BAY, RED	2
L	-	FOCAB 2.5 62/125 DUPLEX ORANGE	1

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		NAME	
mm		0 PLC	\pm -	DWN	GIRIYAPPA. M	12 SEP 05	Tyco Electronics Corporation
		1 PLC	\pm -	CHK	DIWAKAR BELAVADI	13 FEB 06	FOBU, Bangalore, India
		2 PLC	\pm -	APVD	DIWAKAR BELAVADI	13 FEB 06	
		3 PLC	\pm -	PRODUCT SPEC			
		4 PLC	\pm -	APPLICATION SPEC			
		ANGLES	\pm -				
MATERIAL		FINISH		WEIGHT	-	SIZE	A2
						CAGE CODE	00779
						DRAWING NO	C=5349574
						RESTRICTED TO	-
						SCALE	NTS
						SHEET	1 OF 1
						REV	C

AMP 1471-9 REV 31MAR2000

5349574

B

A