




**CONNECTORS**

**BOARD-TO-BOARD CONNECTOR HOUSINGS**



✓ Active

TE CONNECTIVITY (TE)

## 09P EDGE CONN HSG, BIF-LEAF

AMP | BF , HSM

640136-9

TE Internal Number: 640136-9

EU RoHS Compliant

EU ELV Compliant

**Connector Style** Receptacle

**Number of Positions** 9

**Centerline (Pitch)** 3.96 mm [ .156 in ]

**Number of Rows** 1

[↓ PRODUCT DRAWING](#)  
English

[↓ 3D PDF](#)

### DOCUMENTATION

Product Drawings

#### **HOUSING, EDGE CONNECTOR, BIFURCATED LEAF**

PDF

**English**

CAD Files

#### **3D PDF**

PDF

**English**

#### **Customer View Model**

2D\_DXF.ZIP

**English**

#### **Customer View Model**

3D\_IGS.ZIP

**English**

### **Customer View Model**

3D\_STP.ZIP

**English**

---

Product Specifications

Application Specification

### **Bifurcated Leaf Contact**

TIF

**English**

### **Bifurcated Leaf Contact**

PDF

**English**

Product Specification

### **Connector, Edge, Bifurcated Leaf**

TIF

**English**

### **Connector, Edge, Bifurcated Leaf**

PDF

**English**

---

Product Environmental Compliance

TE Material Declaration

### **MD\_640136-9\_03012012020**

PDF

**English**

---

Instruction Sheets

Instruction Sheet (U.S.)

### **BIFURCATED LEAF CONTACT CONNECTORS**

TIF

**English**

### **BIFURCATED LEAF CONTACT CONNECTORS**

PDF

**English**

---

Agency Approvals

Agency Approval Document

### **BIFURCATED LEAF CONNECTOR REPORT**

PDF

**English**

CSA Certificate

### **BIFURCATED LEAF CONNECTOR REPORT**

PDF

**English**

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

### Product Type Features

**Connector Style** Receptacle

---

### Configuration Features

**Number of Positions** 9

**Number of Rows** 1

**Stamped** No

**Keyed** No

---

### Contact Features

**Contact Type** Socket

---

### Mechanical Attachment

**Mating Alignment Type** Polarization

**Mounting Ears** Without

**Mating Alignment** With

---

### Housing Features

**Centerline (Pitch)** 3.96 mm [ .156 in ]

**Housing Material** Polyester

**Housing Color** Natural

---

### Industry Standards

**UL Flammability Rating** UL 94V-0

---

## PRODUCT COMPLIANCE



### Statement of Compliance

**Statement of Compliance**

PDF

---