



Search bar: What can we help you find?

Home > Products > D-Subminiature Connectors > Product Feature Selector > Product Details

748507-1 Product Details

Share | Print | Email



748507-1

TE Internal Number: 748507-1

Active

Standard Cable Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Product Series = HDP-20 (Crimp Snap)
- 15 Positions
- Without Enclosure
- Connector Style = Receptacle

[View all Features](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ View Mating Products (7)
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- RECEPTACLE ASSEMBLY, SIZE 2, 15 POSN, W/ SLIDELATCH,... (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- AMPLIMITE HDP-20 Subminiature D Connector With F Cri... (PDF, English)

Application Specifications:

- AMPLIMITE HDP-20 and Economy Crimp Snap Subminiature... (PDF, English)

Instruction Sheets:

- AMPLIMITE High Density (HDP-20) Connectors with Crim... (PDF, English)
- AMPLIMITE* HIGH DENSITY (HDP-20) CONNECTORS WITH PRE... (PDF, English)

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling
- Mating Products (7)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Product Series = HDP-20 (Crimp Snap)
- Mating Connector Lock = With
- Mating Connector Lock Type = Slide Latches
- Shell Size = 2
- Shell Type = Full Metal Shell
- Grounding Indents = Without
- Grade = Standard
- Color = Black
- Shell Material = Steel

Body Features:

- Shell Plating = Tin
- Insert Material = Thermoplastic

Contact Features:

- Contact Size = 20

Housing Features:

- Enclosure = Without
- Connector Style = Receptacle

Configuration Features:

- Number of Positions = 15
- Preloaded = No

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Insert Flammability Rating = UL 94V-0

Other:

- Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

