


2-1735481-4 Product Details

[Share](#) | [Print](#) | [Email](#)


0.8mm Free Height

0.8FH,R17H.5,100,30/Sn,TU,SC

2-1735481-4

TE Internal Number: 2-1735481-4

Active
[View 3D PDF](#)

Product Highlights [View All](#)

- Connector Style = Receptacle
- 100 Positions
- PCB Mounting Orientation = Vertical
- Board-to-Board Stack Height = 17.00 mm, 18.00 mm, 19.00 mm, 20.00 mm
- Gold (30) Contact Plating, Mating Area, Material

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#) | [Additional Images](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features

PCB Mounting Orientation	Vertical
Family Name	Free Height
Keyed	Yes
Sealant	Without
Cover Material	Steel

Dimensions

Board-to-Board Stack Height (mm [in])	17.00 [0.669], 18.00 [0.709], 19.00 [0.748], 20.00 [0.787]
Height	17H

Body Features

Locating Post(s)	With
Vacuum Cover	With
Locating Post Length	0.5 mm

Contact Features

Contact Plating, Mating Area, Material	Gold (30)
Contact Base Material	Copper Alloy
Solder Tail Contact Plating	Tin over Nickel

Housing Features

Connector Style	Receptacle
Housing Color	Natural
Housing Material	LCP (Liquid Crystal Polymer)
Housing Material Temperature	High

Configuration Features

Number of Positions	100
Number of Rows	Dual

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Reflow solder capable to 245°C, Reflow solder capable to 260°C
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Tube
------------------	------

Other

Brand	AMP
-------	-----

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[View Mating Products \(20\)](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

