




What can we help you find?

Home > Products > RF & Coax > Product Feature Selector > Product Details

## 226176-4 Product Details

Share Print Email



226176-4

TE Internal Number: 226176-4

Active

View 3D PDF

### BRAID-PIC, RF Connectors

Not EU RoHS or ELV Compliant (Find RoHS Compliant Alternates)

#### Product Highlights:

- Terminal
- Coaxial Cable Type (RG/U or Mfg.) = 174, 179, 179A, 179B, 187, 187A, 188, 188A, 316
- Crimp Type = Braid Termination
- Connection Type = Permanent
- Packaging Method = Loose Piece

[View all Features](#)

#### Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List Request Sample Find Similar Products Buy Product

### Documentation & Additional Information

#### Product Drawings:

- [BRAID-PIC P.C. BOARD GROUND TERMINAL SINGLE CRIMP-SI...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- [AMP\\* BRAID-PIC TERMINALS FOR PRINTED CIRCUIT BOARD A...](#) (PDF, English)

#### CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version N)
- 3D Model (IGES, Version N)
- 3D Model (STEP, Version N)

#### Related Products:

- Tooling

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Terminal

#### Termination Features:

- Crimp Type = Braid Termination
- Connection Type = Permanent
- Coaxial Cable Termination Type = Crimp

#### Body Features:

- Body Material = Brass
- Body Plating = Tin-Lead

#### Configuration Features:

- Coaxial Cable Type (RG/U or Mfg.) = 174, 179, 179A, 179B, 187, 187A, 188, 188A, 316

#### Industry Standards:

- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not reviewed for lead free solder process

#### Packaging Features:

- Packaging Method = Loose Piece

#### Other:

- Brand = AMP
- Comment = Loose form parts with preformed tabs.

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

