



CONNECTORS

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HOUSINGS



✓ Active

TE CONNECTIVITY (TE)

ASSY, PLUG, 2X3, SEALED, 0.64, OPEN

Generation Y Connector System

1924211-1

TE Internal Number: 1924211-1

EU RoHS Compliant

EU ELV Compliant

Connector Style Housing for female terminals

Mating Tab Width .64 mm [.025 in]

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire

Number of Positions 6

Centerline (Pitch) 2.54 mm [.1 in]

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

PLUG ASSEMBLY, 6 POSITION, 2x3, SEALED, 0.64mm

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Instruction Sheets

Instruction Sheet (U.S.)

6-Position 0.64mm Sealed Inline Connectors

PDF

English

Repositioning Terminal Position Assurance (TPA) Of 6-Position 0.64mm Sealed Inline Plug Assembly

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Housing for female terminals

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire

Sealable Yes

Hybrid Connector No

Primary Locking Feature Integrated in Housing

Strain Relief No

Row-to-Row Spacing 2.54 mm [.1 in]

Configuration Features

Number of Positions 6

Number of Rows 2

Body Features

Color Gray

Cable Exit Angle 180°

Body Material PA GF

Contact Features

Mating Tab Width .64 mm [.025 in]

Mechanical Attachment

Mounting Feature No

Terminal Position Assurance Yes

Polarized Yes

Housing Features

Centerline (Pitch) 2.54 mm [.1 in]

Dimensions

Width 23.2 mm [.913 in]

Height 29.32 mm [1.154 in]

Length 28.35 mm [1.116 in]

Usage Conditions

Operating Temperature Range -40 – 125 °C [-40 – 257 °F]

Operation/Application

Circuit Application Signal

Packaging Features

Packaging Method Package

Packaging Quantity 20

Other

Connector Position Assurance Capable Yes

Serviceable Yes

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
