

TTE13E8T1/4 Product Details



TTE13E8T1/4

TE Internal Number: 9-1437562-8

 [Active](#)

Toggle Switches

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- TT (Tiny) Series
- Single Pole - Double Throw Configuration (Pole-Throw)
- Current Rating = 3 A
- Mount Style = Panel
- Termination Type = Wire Lugs

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#) |  [Request Sample](#) |  [Find Similar Products](#) |  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [TOGGLE SWITCH](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Series = TT (Tiny)
- Configuration (Pole-Throw) = Single Pole - Double Throw
- Termination Type = Wire Lugs

Electrical Characteristics:

- Current Rating (A) = 3

Termination Features:

- Seal Type = Terminal Seal (epoxy), Environmental

Body Features:

- Mount Style = Panel

Contact Features:

- Contact Plating = Silver

Housing Features:

- Toggle Style = Locking
- Toggle Length (mm [in]) = 14.40 [0.567]
- Process Sealed = No
- Bushing Style = Splashproof, Threaded
- Bushing Type = 1/4-40

Configuration Features:

- [Operating Function](#) = On Off On

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Other:

- Brand = Alcoswitch
- Comment = Each switch is provided with a disposable boot used only during cleaning operation.

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

