

[Skip to content](#)

[Corporate Home](#) | [Electronic Components](#) | [Segments](#) | [Who We Are](#)

Worldwide



Our commitment. Your advantage.

Search

By:



[Sign In](#) | [Register \(Why Register?\)](#)

[Products](#)



- Connectors
- Electromechanical Components
- Electronic Modules
- Fiber Optics
- Filters
- Identification Labeling Products
- Passive Components
- Power Sources
- RF & Microwave Products
- Tooling Products
- Touch Screen Displays
- Tubing, Molded and Harnessing Products
- Wire, Cable and Cable Assemblies
- List all Product Types

- [Aerospace & Defense](#)
- [Appliance](#)
- [Automotive](#)
- [Communications](#)
- [Computer & Consumer Electronics](#)
- [Industrial & Commercial](#)
- [Instrumentation & Medical Equipment](#)


[By Brand](#)

[A to Z](#)

- [Documentation](#)
  - [Find](#)
  - [Documents & Drawings](#)
  - [Find CAD Models](#)
  - [SPICE/Electrical Models](#)
  - [NAFTA Certificate of Origin](#)
  - [White Papers](#)
- [Resources](#)
  - [RoHS](#)
  - [Compliance & Alternates](#)
  - [Cross Reference Products](#)
  - [Compare Multiple Products](#)
  - [Check Distributor Inventory](#)
  - [Find Authorized Distributors](#)
- [My Account](#)
  - [Sign In](#)
  - [Register](#)
- [Customer Support](#)
  - [Support](#)
  - [RoHS Support Center](#)
  - [Glossary of Terms](#)
  - [eBulletin Newsletter](#)

[Home](#) > [Products](#) > [By Type](#) > [Switches](#) > [Product Feature Selector](#) > Product Details

# 1-1825058-9 Product Details



**1-1825058-9**

 [Active](#)

## DIP, Rotary DIP, SIP Switches and DIP Shunts - Standard

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

### Product Highlights:

- DIP Switch
- PCB Mount Style = Surface Mount
- Single Pole - Single Throw Configuration (Pole-Throw)
- Actuator Style = Extended, Slide
- Not Sealed

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [DIP SWITCH, ADE-SMT SERIES](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- Product Type = DIP Switch
- [PCB Mount Style](#) = Surface Mount
- [Configuration \(Pole-Throw\)](#) = Single Pole - Single Throw
- [Actuator Style](#) = Extended, Slide
- Sealed = No
- [Number of Switches](#) = 8
- Termination Style = Outside "L"

### Body Related Features:

- Series = AD
- Centerline (mm [in]) = 2.54 [0.100]

### Contact Related Features:

- Auto-Insertable = Yes
- Contact Material = Copper Alloy
- Contact Mating Area Plating = Gold Flash

### Housing Related Features:

- Housing Color = Black
- Housing Material = PPS
- Housing Flammability Rating = UL 94V-0

### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

### Other:

- Brand = Tyco Electronics

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© 2007 Tyco Electronics Corporation All Rights Reserved