



What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Removable Memory Products > Product Feature Selector > Product Details

Share Print Email

2201778-1 Product Details



2201778-1

TE Internal Number: 2201778-1

Active

Removable Memory Products

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- 8 Positions
- Format = Micro Secure Digital Card
- Solder Tab Length = 1.5 mm
- Lead Type = Surface Mount - Inline leads
- Operating Function = Push-On Push-Off

[View all Features](#)

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> MICRO SD PUSH PUSH LOW PROFILE TYPE (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> None Available <p>CAD Files:</p> <ul style="list-style-type: none"> None Available 	<p>Related Products:</p> <ul style="list-style-type: none"> Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> Mount Angle = Right Angle PCB Mount Style = Surface Mount Shell Material = Copper Alloy <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> Mounting Style = Bottom (Printed Circuit Board) <p>Termination Features:</p> <ul style="list-style-type: none"> Solder Tab Length (mm [in]) = 1.5 [0.059] <p>Dimensions:</p> <ul style="list-style-type: none"> Height off PCB (mm [in]) = 1.65 [0.065] <p>Body Features:</p> <ul style="list-style-type: none"> Lead Type = Surface Mount - Inline leads <p>Contact Features:</p> <ul style="list-style-type: none"> Contact Plating, Mating Area, Material = Gold Vacuum Tape = With 	<p>Housing Features:</p> <ul style="list-style-type: none"> Housing Color = Black Housing Material = Thermoplastic UL Flammability Rating = UL 94V-0 <p>Configuration Features:</p> <ul style="list-style-type: none"> Number of Positions = 8 Operating Function = Push-On Push-Off <p>Industry Standards:</p> <ul style="list-style-type: none"> RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Not reviewed for lead free solder process RoHS/ELV Compliance History = Always was RoHS compliant <p>Conditions for Usage:</p> <ul style="list-style-type: none"> Format = Micro Secure Digital Card <p>Packaging Features:</p> <ul style="list-style-type: none"> Packaging Method = Tape & Reel <p>Other:</p> <ul style="list-style-type: none"> Brand = TE Connectivity

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

