


280359 Product Details

[Live Product Chat](#)



280359

TE Part Number: 280359

[Active](#)

[Add to Part List](#)

.100 AMPMODU Headers, Housings & Contacts

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Housing
- Not Preloaded
- Number of Positions = 4
- Housing Type = Receptacle
- Number of Rows = Single

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [AMPMODU II rec.HSG. single row, crimp on-snap in \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version Y)
- [3D Model](#) (IGES, Version Y)
- [3D Model](#) (STEP, Version Y)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Housing
- [Number of Positions](#) = 4
- [Mating Connector Lock](#) = With
- [Mating Polarization](#) = With
- [Mating Polarization Method](#) = Latched
- [Keyed](#) = No
- Connector Series = Mod II (Italian Range)
- Wire Termination Type = Crimp
- Mating Connector Lock Type = Detent Latching
- Housing Configuration = Both Ends Closed

Mechanical Attachment:

- Preloaded = No

Body Related Features:

- [Housing Type](#) = Receptacle
- [Number of Rows](#) = Single
- [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 [.100]

Housing Related Features:

- [Housing Color](#) = Black
- Housing Flammability Rating = UL 94V-1
- Housing Material = Thermoplastic

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Quantity = 1,000

Other:

- Brand = AMP