


36490 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



36490

Active

Splices - Closed Barrel

Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

Product Highlights:

- ? Splice
- ? Not Sealed
- ? Splice Type = Parallel
- ? Body Style = SOLISTRAND
- ? Uninsulated

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [PROLONGATEUR PARALLELE](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version 0)
- ? [3D Model](#) (IGES, Version 0)
- ? [3D Model](#) (STEP, Version 0)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Splice
- ? [Sealed](#) = No
- ? [Splice Type](#) = Parallel
- ? [Body Style](#) = SOLISTRAND
- ? [Insulation](#) = No
- ? [Insulation Support](#) = Non -Insulation Support
- ? [Material](#) = Copper
- ? [Finish](#) = Tin
- ? Color = None

Mechanical Attachment:

- ? Inside Diameter (mm [in]) = 2.16 [0.085]

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 0.30 -2.00 ² [22-14]
- ? [Wire Range \(CMA\)](#) = 509 - 5,180
- ? Stock Thickness (mm [in]) = 0.69 [0.027]
- ? Outside Diameter (mm [in]) = 3.58 [0.141]

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? [Packaging Method](#) = Loose Piece

Other:

- ? Brand = Tyco Electronics