

[My Cart](#)[My Part Lists](#)[Sign In/Register](#)[English \(Change\)](#)**Have a Question?**

Chat with a Product Information Specialist

[Products](#)[Industries](#)[Resources](#)[About TE](#)[Support Center](#)[My Account](#)[Home](#) > [Products](#) > [Switches & Knobs](#) > [Product Feature Selector](#) > Product Details[Share](#)[Print](#)[Email](#)

3-1825136-5 Product Details

**3-1825136-5**

TE Internal Number: 3-1825136-5

Active

Toggle Switches

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- A Series
- Single Pole - Double Throw Configuration (Pole-Throw)
- Current Rating = 5 A
- Mount Style = Through-Hole
- Termination Type = Vertical Right Angle

[View all Features](#)[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [GEMINI A SERIES TOGGLE SWITCH, SINGLE POLE, 2 POSITI...](#) (PDF, English)

Catalog Pages/Data Sheets:

- [SWITCHES_CORE_PROGRAM_CATALOG](#) (PDF, English)
- [GEMINI SERIES SWITCHES QUICK REF GUIDE 2-1773458-5](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Product Photo](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole-Throw) = Single Pole - Double Throw
- Termination Type = Vertical Right Angle

Electrical Characteristics:

- Current Rating (A) = 5

Termination Related Features:

- Seal Type = Terminal Seal (epoxy)

Body Related Features:

- Series = A
- Mount Style = Through-Hole

Contact Related Features:

- Contact Plating = Silver

Housing Related Features:

- Toggle Actuation = Vertical
- Toggle Style = Baton Long
- Toggle Length (mm [in]) = 12.19 [0.480]
- Process Sealed = No
- Bushing Style = Unthreaded
- Bushing Type = Plain

Configuration Related Features:

- [Operating Function](#) = On On

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Alcoswitch

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Sign up for our eNewsletter

 

Follow Us On:



Visit Us On:

