

TE CONNECTIVITY (TE)
AV19 SPL 5A POWER LED BLUE 12V

Alcoswitch | Alcoswitch AV

AV1911P712Q04
 TE Internal Number: 3-2213766-7

EU RoHS Compliant

EU ELV Compliant

Configuration (Pole-Throw) **Single Pole - Double Throw**

Number of Actuators **Single**

Bushing Style **Threaded**

Illuminated **Yes**

Process Sealed **Yes**

> [See All Features](#)

✓ Active

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

> [See All Documentation](#)

North America ▼

DISTRIBUTOR	QUANTITY	DATE AS OF	
DIGI-KEY ELECTRONICS 1-800-344-4539	162	2017/09/09	>
MOUSER ELECTRONICS (800) 346-6873	52	2017/09/10	>

GET SAMPLE	
SAVE TO LIST ▼	
FIND SIMILAR PRODUCTS	

DOCUMENTATION

FEATURES

PRODUCT COMPLIANCE

Product Drawings

[ANTI-VANDAL SWITCH 19mm POWER LOGO LED](#)

PDF
English

CAD Files

[3D PDF](#)

PDF
3D

[Customer View Model](#)

2D_DXF.ZIP
English

[Customer View Model](#)

3D_IGS.ZIP
English

[Customer View Model](#)

3D_STP.ZIP
English

Agency Approvals

UL Report

Anti Vandal Switches

PDF

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Dust Proof	Yes
Illuminated	Yes
Actuator Style	Round
Product Type	Switch
Switch Type	Pushbutton

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Tactile	No
Operating Function	Push-On/Push-Off
Detent Style	Audible
ESD Grounding Terminal	Without

Electrical Characteristics

Voltage Rating (VAC)	250
----------------------	------------

Body Features

Case Material	PBT
Bushing Style	Threaded
Actuator Profile	Flush

Contact Features

Contact Current Rating (A)	5
Contact Plating	Silver

Termination Features

Termination Type	Wire Lugs
------------------	------------------

Mechanical Attachment	Mounting Type	Panel
	Mounting Angle	Vertical
Housing Features	Process Sealed	Yes
Dimensions	Bushing Length (in)	19
Statement of Compliance	Statement of Compliance PDF	

Compatible Products





[Contact Product Support](#)

Also in the Series | [Alcoswitch AV](#)



[Pushbutton Switches \(966\)](#)

Customers Also Bought

RIBBON CABLE CONNECTORS	TERMINAL BLOCK HEADERS & RECEPTACLES	CARD EDGE POWER CONNECTORS	SWITCH KNOBS
 <p>16P.MICRO-MATCH MOB 8-215464-6</p>	 <p>2 POS 5.08MM R/A PLUG, TRM BLK 796635-2</p>	 <p>CONN SEC II 15 POS 100C/L 5530841-2</p>	 <p>PKB70B1/4=KNOB PLASTIC W/SKIRT PKB70B1/4</p>

[About TE Connectivity](#)

[For Partners](#)

[Customer Support](#)

[CALL US](#)

[LIVE CHAT](#)

[United States](#)