


0721 Product Details

 [Share](#) |
  [Print](#) |
  [Email](#)



0721
(1437394-8)

TE Internal Number: 1437394-8

 **Superseded**

[Search for Replacement Parts](#)

NEMA Terminal Blocks

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- 700 Series Block Series
- NEMA Product Line
- Block Type = Dovetail Base
- Contact Configuration = Strap Screw
- Medium Duty Application

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#) |
  [Request Sample](#) |
  [Find Similar Products](#) |
  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Line Drawing](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Line = NEMA
- Screw Size = 6-32 Slotted Binding Head

Electrical Characteristics:

- Voltage Rating (VAC) = 600
- Amperes (A) = 35.0

Body Features:

- [Block Series](#) = 700 Series
- [Block Type](#) = Dovetail Base
- Mount Style = Channel Mount (Dovetail Base)
- [Wire Range \(Solid and Stranded\)\[MCM\] \(AWG\)](#) = 22-10
- [Blown Fuse Indicator](#) = Without
- [Blown Fuse Indicator Type](#) = None

Contact Features:

- Contact Configuration = Strap Screw
- Pitch (mm [in]) = 9.53 [0.375]

Housing Features:

- [Housing Material](#) = Nylon (Painted)

Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

Operation/Application:

- Application = Medium Duty

Packaging Features:

- Terminals Per Foot = 30

Other:

- Brand = Buchanan

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 

