

Warning Labels: Vinyl, Black on Yellow, 0.5 in H x 0.5 in W

Warning Labels: Vinyl, Black on Yellow, 0.5 in H x 0.5 in W



Product Highlights:

Dimensions:

0.5 in H x 0.5 in W x 0.004 in D

Part Number:

60190

ADD TO CART

1



POPULAR PRODUCTS IN SEARCH ONLY PRODUCTS

OVERVIEW

B-946 vinyl is printed with weather resistant inks and is suited for use in outdoor applications where weatherability is a key consideration.

- Designed for permanent applications in severe indoor or outdoor environments
- High gloss, durable, flexible vinyl with a permanent cold temperature pressure sensitive acrylic adhesive
- Good chemical, oil and water resistance
- Average outdoor durability 8-10 years

SPECIFICATIONS

| | |
|--------------------------------|----------------------------------|
| Material Number | B-946 |
| Cards or Sheets per Pack | 10 |
| Catalog Page # | 234 |
| Dimensions | 0.5 in H x 0.5 in W x 0.004 in D |
| UOM | Pack of 10 Cards |
| Finish | Gloss |
| Illumination | Not Illuminated |
| Indoor or Outdoor Use | Outdoor Use |
| Laminated | Not Laminated |
| Maximum Service Temperature °F | 180 °F |
| Minimum Service Temperature °F | -40 °F |
| PSPA Photoluminescence Class | Not Illuminated |
| Product Number | 60190 |
| UPC | 754473601904 |
| Quantity per Card or Sheet | 10 |
| Reverse Legend | No Reverse Text |
| Thickness | 0.004 in |

| | |
|-----------------------|---|
| Adhesive Type | Acrylic |
| Color | Black on Yellow |
| Header | No Header |
| Label Properties | Aggressive Adhesive Labels, Permanent Adhesive Labels, Standard High Quality Labels |
| Language | No Text |
| Material | Vinyl |
| Mounting Type | Self-Adhesive |
| Reflective Type | Non-Reflective |
| Resistance Properties | Abrasion-Resistant, Chemical-Resistant |
| Reverse Header | No Reverse Header |
| Shape | Triangle |
| Text Legend | No Text |

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Website Feedback](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

Corporate


[About](#)
[Careers](#)
[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)

Other BradyContact Sites

[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software](#)
[Smart ID Brand Protection Solutions](#)

6555 W. Good Hope Rd. Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CT Monday - Thursday; Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 © Brady Worldwide, Inc.