




1530 Series Number and Letter Labels

1530 Series Number and Letter Labels




Product Highlights

Text Legend:

5

Part Number:

ADD TO CART 1



Add To Favorites

You May Also Like



Overview

B-946 vinyl is printed with weather resistant inks and is suited for use in outdoor applications where weatherability is a key consideration.

- Designed for permanent applications in severe indoor or outdoor environments
- High gloss, durable, flexible vinyl with a permanent cold temperature pressure sensitive acrylic adhesive
- Good chemical, oil and water resistance
- Average outdoor durability 8-10 years

Specifications

Material Number	B-946
Country of Origin	MX - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
Cards or Sheets per Pack	1
Catalog Page #	224
Character Height	1 in
Character Width	0.577 in
Dimensions	1.5 in H x 0.875 in W
UOM	Card of 10 Labels
Finish	Gloss
Indoor or Outdoor Use	Outdoor Use
Maximum Service Temperature °F	180 °F
Minimum Service Temperature °F	-40 °F
PSPA Photoluminescence Class	Not Illuminated
Product Number	15305
UPC	754473153052
Quantity per Card or Sheet	10
Thickness	0.004 in
UNSPSC	55121721
Adhesive Type	Acrylic
Applications	General & Industrial ID, Pipe & Valve Marking, Safety & Compliance ID
Color	Black on Yellow
Label/Media Format	Die-Cut on Cards
Label Properties	Aggressive Adhesive Labels, Permanent Adhesive Labels, Standard High Quality Labels
Material	Vinyl
Printer and Label Applications	General Identification, Pipe Marker
Reflective Type	Non-Reflective
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, UV-Resistant, Weather-Resistant

Solutions

Floor Marking Guide
 GHS Label Compliance
 Lockout Tagout Compliance
 Arc Flash Labeling Requirements
 Cable and Wire Label Options
 Product and Barcode Labeling

Services

Lockout Tagout Services
 Arc Flash Services
 Confined Space Services
 Software Programming & Integration
 Label Template & File Conversion
 Printer Use & Training
 Printer Preventative Maintenance
 Toll and Custom Coating
 Authentication & Tracking Services

Help

Contact Us
 Website Feedback
 Knowledge Center
 Printer Drivers & Firmware
 Brady Software Updates
 Safety Data Sheets
 Technical Data Sheets
 WEEE-RoHS Compliance
 Product Certification
 Printer Registration

Resources

Find a Distributor
 Design Custom Safety Signs
 Create Custom THT Labels
 Printer Selection Tool
 Label Selection Tool
 Digital Catalog
 Request a Catalog
 Interactive Facility Map
 EPA e-Manifest Update

Corporate Other BradyContact

[About](#)

[Careers](#)

[Investors](#)

[Privacy](#)

[Policy](#)

[Terms and](#)

[Conditions](#)

[Terms of](#)

[Use](#)

[ISO](#)

[Certificates Solutions](#)

[Sites](#)

[Distributor](#)

[Portal](#)

[International](#)

[Sites](#)

[Safety](#)

[Services &](#)

[Software](#)

[Brand](#)

[Protection](#)

[Solutions](#)

6555 W.

Good Hope Rd.

Milwaukee, WI 53223

Phone: 888-250-3082

Hours: 7am-6pm CT


Monday -

Thursday;

Friday 7am-

5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2019 © Brady Worldwide, Inc.