




Steam Pipe Marker

Steam Pipe Marker



Product Highlights


Overall Size:

Fits Pipes 0.75" Dia. Thru 1.375" Dia.

Part Number:


4129-A

ADD TO CART 1




Add To Favorites


You May Also Like




Steam Pipe



Steam Pipe



Steam Pipe



Steam Pipe



Overview

The ASME (ANSI) Standard for pipe identification is a widely used guideline in determining pipe identification requirements.

- Designed for general purpose pipe identification
- May be applied to dirty, oily, greasy or rough surfaces
- Meets ASME (ANSI) Standard

- Lightweight coiled plastic can be removed and reapplied

Specifications

Arrow Direction	Right
Average Outdoor Durability	5 to 8 Years
Material Number	B-915
Country of Origin	US - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
Character Height	0.5 in
Dimensions	0.8125 in H x 0.8125 in W
UOM	Each
Indoor or Outdoor Use	Outdoor Use
Maximum Outside Pipe Diameter	1.375 in
Maximum Service Temperature °F	140 °F
Minimum Outside Pipe Diameter	0.75 in
Minimum Service Temperature °F	-40 °F
Overall Size	Fits Pipes 0.75" Dia. Thru 1.375" Dia.
Pipe Marker Mounting Style	Snap-On
Pre-Printed Areas on Label	Pipe Contents
PSPA Photoluminescence Class	Not Illuminated
Product Number	41607
UPC	754473416072
Trade Name	BradySnap-On™
UNSPSC	55121737
Applications	Pipe & Valve Marking
Color	Black on Yellow
Label Properties	Harsh Environment Labels
Language	English

Material	Plastic
Pictogram Description	Directional Arrow Symbol
Printer and Label Applications	Pipe Marker
Reflective Type	Non-Reflective
Resistance Properties	Abrasion-Resistant, Chemical-Resistant
Size	A
Text Legend	STEAM

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Website Feedback](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Create Custom THT Labels](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

Corporate

[About](#)
[Careers](#)
[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)

Other BradyContact Sites

[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software Brand Protection Solutions](#)

6555 W. Good Hope Rd. Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CT Monday - Thursday; Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2019 © Brady Worldwide, Inc.