

## Complete units: Selector switches $\varnothing$ 22MM



Technical Info (p. 103)

### ▶ SELECTOR SWITCHES - NON-ILLUMINATED

#### WITH HANDLE


2 positions

Chrome Bezel  
Part Number

Black Bezel  
Part Number



L21KE03-1E10



#### MAINTAINED POSITIONS - 45°

● Red	NC	
● Green	NO	
● Black	NO	
● Black	2 NO	
● Black	NO + NC	
● Grey	NO	



L21KA01-1E01
L21KA02-1E10
L21KA03-1E10
L21KA03-3E20
L21KA03-3E11
L21KA08-1E10

L22KA01-1E01
L22KA02-1E10
L22KA03-1E10
L22KA03-3E20
L22KA03-3E11
L22KA08-1E10

#### SPRING RETURN - 45°

● Red	NC	
● Green	NO	
● Black	NO	
● Black	2 NO	
● Black	NO + NC	
● Grey	NO	



L21KB01-1E01
L21KB02-1E10
L21KB03-1E10
L21KB03-3E20
L21KB03-3E11
L21KB08-1E10

L22KB01-1E01
L22KB02-1E10
L22KB03-1E10
L22KB03-3E20
L22KB03-3E11
L22KB08-1E10

#### MAINTAINED POSITIONS - 90°

● Red	NC	
● Green	NO	
● Black	NO	
● Black	2 NO	
● Black	NO + NC	
● Grey	NO	



L21KE01-1E01
L21KE02-1E10
L21KE03-1E10
L21KE03-3E20
L21KE03-3E11
L21KE08-1E10


L22KE01-1E01
L22KE02-1E10
L22KE03-1E10
L22KE03-3E20
L22KE03-3E11
L22KE08-1E10

#### WITH HANDLE

3 positions



L21MA03-3E20



#### MAINTAINED POSITIONS - 45°

● Red	2 NO	
● Green	2 NO	
● Black	2 NO	
● Grey	2 NO	



L21MA01-3E20
L21MA02-3E20
L21MA03-3E20
L21MA08-3E20

L22MA01-3E20
L22MA02-3E20
L22MA03-3E20
L22MA08-3E20

#### SPRING RETURN - 45°

● Red	2 NO	
● Green	2 NO	
● Black	2 NO	
● Grey	2 NO	



L21MD01-3E20
L21MD02-3E20
L21MD03-3E20
L21MD08-3E20

L22MD01-3E20
L22MD02-3E20
L22MD03-3E20
L22MD08-3E20

#### MAINTAINED / SPRING RETURN - 45°

● Red	2 NO	
● Green	2 NO	
● Black	2 NO	
● Grey	2 NO	



L21MC01-3E20
L21MC02-3E20
L21MC03-3E20
L21MC08-3E20

L22MC01-3E20
L22MC02-3E20
L22MC03-3E20
L22MC08-3E20