

Complete units: Pushbuttons \varnothing 22mm


 Technical Info (p. 103)

► SPRING RETURN - ILLUMINATED

FLUSH



L21AH20-3EAGL1



LED blocks

12/24 Vac/dc

● Red	NO+NC
● Green	NO+NC
● Yellow	NO+NC
○ White	NO+NC
● Blue	NO+NC

Chrome Bezel
Part Number

Black Bezel
Part Number

L21AH10-3EARL11	L22AH10-3EARL11
L21AH20-3EAGL11	L22AH20-3EAGL11
L21AH40-3EAYL11	L22AH40-3EAYL11
L21AH50-3EAWL11	L22AH50-3EAWL11
L21AH60-3EABL11	L22AH60-3EABL11

130 Vac


● Red	NO+NC
● Green	NO+NC
● Yellow	NO+NC
○ White	NO+NC
● Blue	NO+NC

L21AH10-3EARM11	L22AH10-3EARM11
L21AH20-3EAGM11	L22AH20-3EAGM11
L21AH40-3EAYM11	L22AH40-3EAYM11
L21AH50-3EAWM11	L22AH50-3EAWM11
L21AH60-3EABM11	L22AH60-3EABM11

PROJECTING



L21AK40-3EAYM11



LED blocks

12/24 Vac/dc

● Red	NO+NC
● Green	NO+NC
● Yellow	NO+NC
○ White	NO+NC
● Blue	NO+NC

L21AK10-3EARL11	L22AK10-3EARL11
L21AK20-3EAGL11	L22AK20-3EAGL11
L21AK40-3EAYL11	L22AK40-3EAYL11
L21AK50-3EAWL11	L22AK50-3EAWL11
L21AK60-3EABL11	L22AK60-3EABL11

130 Vac


● Red	NO+NC
● Green	NO+NC
● Yellow	NO+NC
○ White	NO+NC
● Blue	NO+NC

L21AK10-3EARM11	L22AK10-3EARM11
L21AK20-3EAGM11	L22AK20-3EAGM11
L21AK40-3EAYM11	L22AK40-3EAYM11
L21AK50-3EAWM11	L22AK50-3EAWM11
L21AK60-3EABM11	L22AK60-3EABM11

\varnothing 32 MUSHROOM



L21AL10-3EARL11



LED blocks

12/24 Vac/dc

● Red	NO+NC
● Green	NO+NC
● Yellow	NO+NC
○ White	NO+NC
● Blue	NO+NC

L21AL10-3EARL11	L22AL10-3EARL11
L21AL20-3EAGL11	L22AL20-3EAGL11
L21AL40-3EAYL11	L22AL40-3EAYL11
L21AL50-3EAWL11	L22AL50-3EAWL11
L21AL60-3EABL11	L22AL60-3EABL11

130 Vac

● Red	NO+NC
● Green	NO+NC
● Yellow	NO+NC
○ White	NO+NC
● Blue	NO+NC

L21AL10-3EARM11	L22AL10-3EARM11
L21AL20-3EAGM11	L22AL20-3EAGM11
L21AL40-3EAYM11	L22AL40-3EAYM11
L21AL50-3EAWM11	L22AL50-3EAWM11
L21AL60-3EABM11	L22AL60-3EABM11