

Domestic Hot Water Return Pipe Marker



Domestic Hot Water Return Pipe Marker

Part Number:

4052-H

Overall Size:

Fits Pipes 10" Dia. Thru 15" Dia.

Material:

Plastic

ADD TO CART

1

Strap-On Pipe Markers from Brady® are ideal for indoor and outdoor use.

- Designed for general purpose pipe identification on pipes that have a 6 in. or larger diameter, including insulation
- May be applied to dirty, oily, greasy or rough surfaces
- Installs quickly and easily in older facilities or new construction
- Pipe Markers are lightweight and durable and can be removed and reapplied in other areas

SPECIFICATIONS

Anti-Skid Surface?	N/A
Arrow Direction	Right
Average Outdoor Durability	5 to 8 Years
Material Number	B-915
Character Height	3.5 in
Dimensions	10 in H x 32 in W
UOM	Each
Indoor or Outdoor Use	Outdoor Use
Maximum Outside Pipe Diameter	15 in
Maximum Service Temperature °F	140 °F
Minimum Outside Pipe Diameter	10 in
Minimum Service Temperature °F	-40 °F
Overall Size	Fits Pipes 10" Dia. Thru 15" Dia.
Pipe Marker Mounting Style	Strap-On
Pipe Marker Style	H
Pre-Printed Areas on Label	Pipe Contents
PSPA Photoluminescence Class	Not Illuminated
Product Number	40438
UPC	754473404383
Tamper Indication Type	N/A
Adhesive Type	N/A
Applications	Pipe & Valve Marking

Color	Black on Yellow
Language	English
Material	Plastic
Material Properties	N/A
Pictogram Description	Directional Arrow Symbol
Reflective Type	Non-Reflective
Resistance Properties	Abrasion-Resistant, Chemical-Resistant
Size	H
Text Legend	DOMESTIC HOT WATER RETURN

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Visual Workplace Services](#)
[Hazcom GHS Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)



Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance

Contact
 6555 W. Good Hope Rd. Milwaukee WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CST
Monday - Friday

About
[Corporation](#)
[Privacy](#)
[Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)

Other
[Brady Sites](#)
[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software](#)
[Smart ID](#)
[Brand Protection](#)



© 2017 Brady Worldwide, Inc.

**and include
high-
performance
labels,
signs, safety
devices,
printing
systems
and
software.**