

Complete units: Pilot lights \varnothing 22MM


▶ PILOT LIGHTS

 Technical Info (p.103)

HEAD, CLIP AND MODULE



L20SE20-1EAGL



LED blocks

- Red
- Green
- Yellow
- White
- Blue

12/24 Vac/Dc
 L20SE10-1EARL
 L20SE20-1EAGL
 L20SE40-1EAYL
 L20SE50-1EAWL
 L20SE60-1EABL

130Vac
 L20SE10-1EARM
 L20SE20-1EAGM
 L20SE40-1EAYM
 L20SE50-1EAWM
 L20SE60-1EABM

230Vac
 L20SE10-1EARH
 L20SE20-1EAGH
 L20SE40-1EAYH
 L20SE50-1EAWH
 L20SE60-1EABH


Ribbed Lens
Part Number

Smooth Lens
Part Number

ONE-PIECE PILOT PLIGHTS - SUPPLIED WITH LED BULBS



L20SA40LA



6 Vac/dc

- Red
- Green
- Clear
- Yellow
- White
- Blue

L20SA10CA
 L20SA20CA
 L20SA30CA
 L20SA40CA
 L20SA50CA
 L20SA60CA

L20SA10C
 L20SA20C
 L20SA40C
 L20SA50C
 L20SA60C

12 Vac/dc

- Red
- Green
- Clear
- Yellow
- White
- Blue

L20SA10JA
 L20SA20JA
 L20SA30JA
 L20SA40JA
 L20SA50JA
 L20SA60JA

L20SA10J
 L20SA20J
 L20SA40J
 L20SA50J
 L20SA60J



L20SA10M

24 Vac/dc

- Red
- Green
- Clear
- Yellow
- White
- Blue

L20SA10LA
 L20SA20LA
 L20SA30LA
 L20SA40LA
 L20SA50LA
 L20SA60LA

L20SA10L
 L20SA20L
 L20SA40L
 L20SA50L
 L20SA60L

120 Vac

- Red
- Green
- Clear
- Yellow
- White
- Blue

L20SA10MA
 L20SA20MA
 L20SA30MA
 L20SA40MA
 L20SA50MA
 L20SA60MA

L20SA10M
 L20SA20M
 L20SA40M
 L20SA50M
 L20SA60M

240 Vac

- Red
- Green
- Clear
- Yellow
- White
- Blue

L20SA10HA
 L20SA20HA
 L20SA30HA
 L20SA40HA
 L20SA50HA
 L20SA60HA

L20SA10H
 L20SA20H
 L20SA40H
 L20SA50H
 L20SA60H