

[Labels](#) / [Printer Labels and Ribbons](#) / [Desktop Printer Ribbons and Ink Cartridges](#) / [BBP30 Sign and Label Printer Ribbons](#) /

B30 Series R4500 Printer Ribbon



B30 Series R4500 Printer Ribbon

Part Number:

B30-R4500-SV

Ribbon Size:

4.33 in W x 200 ft L

Color:

Silver

For Use with Printer:

BBP®30 Label Printer, BBP®31 Sign and Label Printer, BBP®33 Label Printer, BBP®35 Multi-Color Sign and Label Printer, BBP®37 Color & Cut Sign and Label Printer

[ADD TO CART](#)

1

PEOPLE ALSO VIEWED

OVERVIEW

B30 Series "Drop & Click" print ribbons enable 5-second ribbon supply changes. No calibrating, no threading, no waste, no hassles and the ink always faces the right direction!

- One-color ribbon for printing a single color onto a label
- R4500 Series colored resin/wax ribbons offer smear resistance and chemical resistance when printed on the appropriate label material from Brady®
- Recommended for printing on paper and films that have a matte or rough surface, such as B-427 Self-Laminating Vinyl and B-499 Nylon Cloth from Brady®
- Self-contained B30 Series cartridges drop straight into the printer with a "click"

SPECIFICATIONS

UOM	Roll of 200 Feet
Product Number	118923
UPC	662820981527
Ribbon Color Options	Single Color Ribbon
Ribbon Formulation Type	Resin/Wax
Ribbon Roll Type	Ribbon in Cartridge
Ribbon Series	R4500
Ribbon Size	4.33 in W x 200 ft L
Ribbon Size(m)	109.98 mm W x 60.96 m L
Ribbon Width	4.33 in
Roll Length	200 ft
Trade Name	B30
Color	Silver
For Use with Printer	BBP®30 Label Printer, BBP®31 Sign and Label Printer, BBP®33 Label Printer, BBP®35 Multi-Color Sign and Label Printer, BBP®37 Color & Cut Sign and Label Printer
Label/Media Format	Ribbon in Printer Specific Cartridge
Patent Number(s)	6860658, D480749
Resistance Properties	Chemical-Resistant, Smear-Resistant

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)

Help

[Contact Us](#)
[Knowledge Center](#)

Resources

[Find a Distributor](#)
[Printer Selection Tool](#)

Lockout Tagout Compliance

Arc Flash Labeling Requirements

Cable and Wire Label Options

Product and Barcode Labeling

Brand Protection Solutions

Confined Space Services

Visual Workplace Services

Hazcom GHS Services

Software Programming & Integration

Label Template & File Conversion

Printer Use & Training

Printer Preventative Maintenance

Toll and Custom Coating

Authentication & Tracking Services

Printer Drivers & Firmware

Brady Software Updates

Safety Data Sheets

Technical Data Sheets

WEEE RoHS Compliance

Product Certification

Printer Registration

Label Selection Tool

Digital Catalog

Request a Catalog



Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.

Contact
6555 W. Good Hope Rd. Milwaukee WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CST
Monday - Friday

About
[Corporation](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)

Other
[Brady Sites](#)
[Distributor Portal](#)
[International Sites](#)
[Safety Services](#)
&
[Software Smart ID Brand Protection](#)



© 2017 Brady Worldwide, Inc.