

























Connectors M5 x 0,5 / M8 x 1

Connector ESW 05S	Connector ESG 05S	Pin-assignment connector M5 x 0,5																																	
 <p style="text-align: center;">see color code for wiring</p>	 <p style="text-align: center;">see color code for wiring</p>																																		
<p>Part number</p> <table border="0"> <tr> <td>ESW 05SP0200</td> <td>3 pin</td> <td>2 m PUR</td> </tr> <tr> <td>ESW 05SP0500</td> <td>3 pin</td> <td>5 m PUR</td> </tr> </table> <p>- with cap nut</p>	ESW 05SP0200	3 pin	2 m PUR	ESW 05SP0500	3 pin	5 m PUR	<p>Part number</p> <table border="0"> <tr> <td>ESG 05SP0200</td> <td>3 pin</td> <td>2 m PUR</td> </tr> <tr> <td>ESG 05SP0500</td> <td>3 pin</td> <td>5 m PUR</td> </tr> </table> <p>- with cap nut</p>	ESG 05SP0200	3 pin	2 m PUR	ESG 05SP0500	3 pin	5 m PUR	<table border="1"> <thead> <tr> <th>Pin-Nr.</th> <th>Color</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>BN (Brown)</td> </tr> <tr> <td>2</td> <td>n.c.</td> </tr> <tr> <td>3</td> <td>BU (Blue)</td> </tr> <tr> <td>4</td> <td>BK (Black)</td> </tr> </tbody> </table>	Pin-Nr.	Color	1	BN (Brown)	2	n.c.	3	BU (Blue)	4	BK (Black)											
ESW 05SP0200	3 pin	2 m PUR																																	
ESW 05SP0500	3 pin	5 m PUR																																	
ESG 05SP0200	3 pin	2 m PUR																																	
ESG 05SP0500	3 pin	5 m PUR																																	
Pin-Nr.	Color																																		
1	BN (Brown)																																		
2	n.c.																																		
3	BU (Blue)																																		
4	BK (Black)																																		
Connector ESW 08S / ES 8A	Connector ESG 09S / ES 9A	Connector ESW 31S																																	
 <p style="text-align: center;">see color code for wiring</p>	 <p style="text-align: center;">see color code for wiring</p>	 <p style="text-align: center;">see color code for wiring</p>																																	
<p>Part number</p> <table border="0"> <tr> <td>ESW 08SH0200</td> <td>3 pin</td> <td>2 m PUR</td> </tr> <tr> <td>ESW 08SH0500</td> <td>3 pin</td> <td>5 m PUR</td> </tr> <tr> <td>ES 8A</td> <td>4 pin</td> <td>2 m PVC</td> </tr> <tr> <td>ES 8A5</td> <td>4 pin</td> <td>5 m PVC</td> </tr> </table> <p>- with clip fastener - PUR, halogen-free</p>	ESW 08SH0200	3 pin	2 m PUR	ESW 08SH0500	3 pin	5 m PUR	ES 8A	4 pin	2 m PVC	ES 8A5	4 pin	5 m PVC	<p>Part number</p> <table border="0"> <tr> <td>ESG 09SH0200</td> <td>3 pin</td> <td>2 m PUR</td> </tr> <tr> <td>ESG 09SH0500</td> <td>3 pin</td> <td>5 m PUR</td> </tr> <tr> <td>ES 9A</td> <td>4 pin</td> <td>2 m PVC</td> </tr> <tr> <td>ES 9A5</td> <td>4 pin</td> <td>5 m PVC</td> </tr> </table> <p>- with clip fastener - PUR, halogen-free</p>	ESG 09SH0200	3 pin	2 m PUR	ESG 09SH0500	3 pin	5 m PUR	ES 9A	4 pin	2 m PVC	ES 9A5	4 pin	5 m PVC	<p>Part number</p> <table border="0"> <tr> <td>ESW 31SH0200</td> <td>3 pin</td> <td>2 m PUR</td> </tr> <tr> <td>ESW 31SH0500</td> <td>3 pin</td> <td>5 m PUR</td> </tr> <tr> <td>ESW 31SH1000</td> <td>3 pin</td> <td>10 m PUR</td> </tr> </table> <p>- with cap nut - halogen-free</p>	ESW 31SH0200	3 pin	2 m PUR	ESW 31SH0500	3 pin	5 m PUR	ESW 31SH1000	3 pin	10 m PUR
ESW 08SH0200	3 pin	2 m PUR																																	
ESW 08SH0500	3 pin	5 m PUR																																	
ES 8A	4 pin	2 m PVC																																	
ES 8A5	4 pin	5 m PVC																																	
ESG 09SH0200	3 pin	2 m PUR																																	
ESG 09SH0500	3 pin	5 m PUR																																	
ES 9A	4 pin	2 m PVC																																	
ES 9A5	4 pin	5 m PVC																																	
ESW 31SH0200	3 pin	2 m PUR																																	
ESW 31SH0500	3 pin	5 m PUR																																	
ESW 31SH1000	3 pin	10 m PUR																																	
Connector ESW 31A	Connector ESG 32S	Connector ESG 32A																																	
 <p style="text-align: center;">see color code for wiring</p>	 <p style="text-align: center;">see color code for wiring</p>	 <p style="text-align: center;">see color code for wiring</p>																																	
<p>Part number</p> <table border="0"> <tr> <td>ESW 31AH0200</td> <td>4 pin</td> <td>2 m PUR</td> </tr> <tr> <td>ESW 31AH0500</td> <td>4 pin</td> <td>5 m PUR</td> </tr> <tr> <td>ESW 31AH1000</td> <td>4 pin</td> <td>10 m PUR</td> </tr> </table> <p>- with cap nut - halogen-free</p>	ESW 31AH0200	4 pin	2 m PUR	ESW 31AH0500	4 pin	5 m PUR	ESW 31AH1000	4 pin	10 m PUR	<p>Part number</p> <table border="0"> <tr> <td>ESG 32SH0200</td> <td>3 pin</td> <td>2 m PUR</td> </tr> <tr> <td>ESG 32SH0500</td> <td>3 pin</td> <td>5 m PUR</td> </tr> <tr> <td>ESG 32SH1000</td> <td>3 pin</td> <td>10 m PUR</td> </tr> </table> <p>- with cap nut - halogen-free</p>	ESG 32SH0200	3 pin	2 m PUR	ESG 32SH0500	3 pin	5 m PUR	ESG 32SH1000	3 pin	10 m PUR	<p>Part number</p> <table border="0"> <tr> <td>ESG 32AH0200</td> <td>4 pin</td> <td>2 m PUR</td> </tr> <tr> <td>ESG 32AH0500</td> <td>4 pin</td> <td>5 m PUR</td> </tr> <tr> <td>ESG 32AH1000</td> <td>4 pin</td> <td>10 m PUR</td> </tr> </table> <p>- with cap nut - halogen-free</p>	ESG 32AH0200	4 pin	2 m PUR	ESG 32AH0500	4 pin	5 m PUR	ESG 32AH1000	4 pin	10 m PUR						
ESW 31AH0200	4 pin	2 m PUR																																	
ESW 31AH0500	4 pin	5 m PUR																																	
ESW 31AH1000	4 pin	10 m PUR																																	
ESG 32SH0200	3 pin	2 m PUR																																	
ESG 32SH0500	3 pin	5 m PUR																																	
ESG 32SH1000	3 pin	10 m PUR																																	
ESG 32AH0200	4 pin	2 m PUR																																	
ESG 32AH0500	4 pin	5 m PUR																																	
ESG 32AH1000	4 pin	10 m PUR																																	









Connectors M8 x 1

Connector	Connector	Connector																		
<p style="text-align: center;">ESW 31AP</p>  <p style="text-align: right;">see color code for wiring</p> <p>Part number ESW 31AP0500G 4 pin 5 m PUR</p> <ul style="list-style-type: none"> - shielded - screen connected with cap nut - PUR, halogen-free 	<p style="text-align: center;">ESG 32AP</p>  <p style="text-align: right;">see color code for wiring</p> <p>Part number ESG 32AP0500G 4 pin 5 m PUR</p> <ul style="list-style-type: none"> - shielded - screen connected with cap nut - PUR, halogen-free 	<p style="text-align: center;">ES 22 / ES 22A</p>  <p>Part number ES 22 3 pin ES 22A 4 pin</p> <ul style="list-style-type: none"> - for self-assembly - with cap nut 																		
<p style="text-align: center;">ES 21 / ES 21A</p>  <p>Part number ES 21 3 pin ES 21A 4 pin</p> <ul style="list-style-type: none"> - for self-assembly - with cap nut 	<p style="text-align: center;">ES 30</p>  <p>Part number ES 30.2 2 pin 2 m PVC</p> <ul style="list-style-type: none"> - for My-Com BS only - with clip fastener 																			
<p style="text-align: center;">Pin-assignment connector 3-pin (M8)</p>  <p style="text-align: center;">viewed from rear of connector</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>Pin-Nr.</th> <th>Color</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>BN (Brown)</td> </tr> <tr> <td>3</td> <td>BU (Blue)</td> </tr> <tr> <td>4</td> <td>BK (Black)</td> </tr> </tbody> </table>	Pin-Nr.	Color	1	BN (Brown)	3	BU (Blue)	4	BK (Black)	<p style="text-align: center;">Pin-assignment connector 4-pin (M8)</p>  <p style="text-align: center;">viewed from rear of connector</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>Pin-Nr.</th> <th>Color</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>BN (Brown)</td> </tr> <tr> <td>2</td> <td>WH (White)</td> </tr> <tr> <td>3</td> <td>BU (Blue)</td> </tr> <tr> <td>4</td> <td>BK (Black)</td> </tr> </tbody> </table>	Pin-Nr.	Color	1	BN (Brown)	2	WH (White)	3	BU (Blue)	4	BK (Black)	
Pin-Nr.	Color																			
1	BN (Brown)																			
3	BU (Blue)																			
4	BK (Black)																			
Pin-Nr.	Color																			
1	BN (Brown)																			
2	WH (White)																			
3	BU (Blue)																			
4	BK (Black)																			



Connectors M12 x 1

<p>Connector ESW 33S</p>	<p>Connector ESW 33A</p>	<p>Connector ESW 33AF</p>
 <p>see color code for wiring</p>	 <p>see color code for wiring</p>	
<p>Part number ESW 33SH0200 3 pin 2 m PUR ESW 33SH0500 3 pin 5 m PUR ESW 33SH1000 3 pin 10 m PUR</p> <p>- with cap nut - halogen-free</p>	<p>Part number ESW 33AH0200 4 pin 2 m PUR ESW 33AH0500 4 pin 5 m PUR ESW 33AH1000 4 pin 10 m PUR</p> <p>- with cap nut - halogen-free</p>	<p>Part number ESW 33AF0500 4 pin 5 m PVC</p> <p>- with stainless steel cap nut</p>
<p>Connector ES 33C</p>	<p>Connector ESG 34S</p>	<p>Connector ESG 34A</p>
 <p>see color code for wiring</p>	 <p>see color code for wiring</p>	 <p>see color code for wiring</p>
<p>Part number ES 33CP2 5 pin 2 m PUR ES 33CP5 5 pin 5 m PUR</p> <p>- with cap nut</p>	<p>Part number ESG 34SH0200 3 pin 2 m PUR ESG 34SH0500 3 pin 5 m PUR ESG 34SH1000 3 pin 10 m PUR</p> <p>- with cap nut - halogen-free</p>	<p>Part number ESG 34AH0200 4 pin 2 m PUR ESG 34AH0500 4 pin 5 m PUR ESG 34AH1000 4 pin 10 m PUR</p> <p>- with cap nut - halogen-free</p>
<p>Connector ESG 34AF</p>	<p>Connector ES 34C</p>	
	 <p>see color code for wiring</p>	
<p>Part number ESG 34AF0500 4 pin 5 m PVC</p> <p>- with stainless steel cap nut</p>	<p>Part number ES 34CP2 5 pin 2 m PUR ES 34CP5 5 pin 5 m PUR</p> <p>- with cap nut</p>	

Connectors M12 x 1

<p>Connector ES 33A</p>	<p>Connector ES 34A</p>	<p>Connector ES 34C</p>
 <p>see color code for wiring</p>	 <p>see color code for wiring</p>	 <p>see color code for wiring</p>
<p>Part number</p> <p>ES 33AP2B 4 pin 2 m PUR ES 33AP5B 4 pin 5 m PUR ES 33AP10B 4 pin 10 m PUR</p> <p>- shielded - screen connected with cap nut</p>	<p>Part number</p> <p>ES 34AP2B 4 pin 2 m PUR ES 34AP5B 4 pin 5 m PUR ES 34AP10B 4 pin 10 m PUR</p> <p>- shielded - screen connected with cap nut</p>	<p>Part number</p> <p>ES 34CP2B 5 pin 2 m PUR ES 34CP5B 5 pin 5 m PUR ES 34CP10B 5 pin 10 m PUR</p> <p>- shielded - screen connected with cap nut</p>
<p>Connector ESG 34F</p>	<p>Connector ES 4A</p>	<p>Connector ES 14 / ES 14C</p>
	 <p>see color code for wiring</p>	
<p>Part number</p> <p>ESG 34FP0200B 8 pin 2 m PUR ESG 34FP0500B 8 pin 5 m PUR</p> <p>- shielded - screen connected with cap nut</p>	<p>Part number</p> <p>ES 4AP5L PNP 4 pin 5 m PUR ES 4AN5L NPN 4 pin 5 m PUR</p> <p>LED 1: +Vs LED 2: output 1</p>	<p>Part number</p> <p>ES 14 PG7 4 pin ES 14C PG7 5 pin</p> <p>- for self-assembly - with cap nut</p>
<p>Connector ES 18 / ES 18C</p>	<p>Connector M12 x 1</p>	<p>Note</p>
		<p>jacket insulation material: Polyetherurethane TPU 11YH1</p> <p>flame retardent according to: IEC 332-2</p> <p>strand insulation: halogen-free</p>
<p>Part number</p> <p>ES 18 PG7 4 pin ES 18C PG7 5 pin</p> <p>- for self-assembly - with cap nut</p>	<p>Part number</p> <p>10135462 5 pin 10146775 8 pin</p> <p>- for self-assembly - screen can be connected with cap nut (necessary for sensors with analog output)</p>	<p>Connectors with halogen-free cables</p> <p>- strands UL-style 10493 - PVC- and halogen-free - suitable for flexible cable carriers</p>

Connectors M12 x 1

Pin-assignment connector 3-pin (M 12)	Pin-assignment connector 4-pin (M 12)	Pin-assignment connector 5-pin (M 12)																																
<div style="text-align: center;">  </div> <p style="text-align: center;">viewed from rear of connector</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">Pin-Nr.</th> <th style="text-align: left;">Color</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>BN (Brown)</td> </tr> <tr> <td>2</td> <td>n.c.</td> </tr> <tr> <td>3</td> <td>BU (Blue)</td> </tr> <tr> <td>4</td> <td>BK (Black)</td> </tr> </tbody> </table>	Pin-Nr.	Color	1	BN (Brown)	2	n.c.	3	BU (Blue)	4	BK (Black)	<div style="text-align: center;">  </div> <p style="text-align: center;">viewed from rear of connector</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">Pin-Nr.</th> <th style="text-align: left;">Color</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>BN (Brown)</td> </tr> <tr> <td>2</td> <td>WH (White)</td> </tr> <tr> <td>3</td> <td>BU (Blue)</td> </tr> <tr> <td>4</td> <td>BK (Black)</td> </tr> </tbody> </table>	Pin-Nr.	Color	1	BN (Brown)	2	WH (White)	3	BU (Blue)	4	BK (Black)	<div style="text-align: center;">  </div> <p style="text-align: center;">viewed from rear of connector</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">Pin-Nr.</th> <th style="text-align: left;">Color</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>BN (Brown)</td> </tr> <tr> <td>2</td> <td>WH (White)</td> </tr> <tr> <td>3</td> <td>BU (Blue)</td> </tr> <tr> <td>4</td> <td>BK (Black)</td> </tr> <tr> <td>5</td> <td>GY (Grey)</td> </tr> </tbody> </table>	Pin-Nr.	Color	1	BN (Brown)	2	WH (White)	3	BU (Blue)	4	BK (Black)	5	GY (Grey)
Pin-Nr.	Color																																	
1	BN (Brown)																																	
2	n.c.																																	
3	BU (Blue)																																	
4	BK (Black)																																	
Pin-Nr.	Color																																	
1	BN (Brown)																																	
2	WH (White)																																	
3	BU (Blue)																																	
4	BK (Black)																																	
Pin-Nr.	Color																																	
1	BN (Brown)																																	
2	WH (White)																																	
3	BU (Blue)																																	
4	BK (Black)																																	
5	GY (Grey)																																	
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">Pin-Nr.</th> <th style="text-align: left;">Color</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>WH (White)</td> </tr> <tr> <td>2</td> <td>BN (Brown)</td> </tr> <tr> <td>3</td> <td>GN (Green)</td> </tr> <tr> <td>4</td> <td>YE (Yellow)</td> </tr> <tr> <td>5</td> <td>GY (Gray)</td> </tr> <tr> <td>6</td> <td>PK (Pink)</td> </tr> <tr> <td>7</td> <td>BU (Blue)</td> </tr> <tr> <td>8</td> <td>RD (Red)</td> </tr> </tbody> </table>	Pin-Nr.	Color	1	WH (White)	2	BN (Brown)	3	GN (Green)	4	YE (Yellow)	5	GY (Gray)	6	PK (Pink)	7	BU (Blue)	8	RD (Red)																
Pin-Nr.	Color																																	
1	WH (White)																																	
2	BN (Brown)																																	
3	GN (Green)																																	
4	YE (Yellow)																																	
5	GY (Gray)																																	
6	PK (Pink)																																	
7	BU (Blue)																																	
8	RD (Red)																																	