


Labels / Inspection and Inventory Labels / Inspection Repair Labels /

Write-on Labels



Write-on Labels

Part Number:

WOX-38

Dimensions:

0.625 in H x 1.5 in W

Material:

Polyester

Color:

Green on White

ADD TO CART

1

PEOPLE ALSO VIEWED

OVERVIEW

This B-619 polyester material is ideal for use as general purpose high performance labels, barcode labels, the topside of printed circuit boards and IC identification.

- Has good smudge resistance, solvent resistance and high temperature performance
- Leaves no adhesive residue when removed, so is ideal for permanent or temporary applications
- Matte finish material with permanent acrylic adhesive can be thermal transfer printed or dot matrix printed
- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC; UL approved; CSA accepted

SPECIFICATIONS

Material Number	B-619
Corner Type	Square Corners
Dimensions	0.625 in H x 1.5 in W
UOM	Card of 14 Labels
Finish	Matte
Maximum Service Temperature °F	293 °F
Minimum Service Temperature °F	-94 °F
Product Number	35638
UPC	662820356387
Quantity per Card or Sheet	14
Thickness	0.0036 in
Write-On?	Yes
Write-On Area?	Yes
Adhesive Type	Acrylic
Applications	Barcode Labeling, Circuit Board ID - Through Hole Top, General & Industrial ID
Color	Green on White
Header	No Header
Label/Media Format	Die-Cut on Cards
Language	English
Material	Polyester
Material Properties	N/A
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, Smear-Resistant, UV-Resistant
Text Legend	TESTED

Solutions

Floor Marking Guide
GHS Label Compliance
Lockout Tagout Compliance
Arc Flash Labeling Requirements
Cable and Wire Label Options
Product and Barcode Labeling
Brand Protection Solutions

Services


Lockout Tagout Services
Arc Flash Services
Confined Space Services
Visual Workplace Services
Hazcom GHS Services
Software Programming & Integration
Label Template & File Conversion
Printer Use & Training
Printer Preventative Maintenance
Toll and Custom Coating
Authentication & Tracking Services

Help

Contact Us
Knowledge Center
Printer Drivers & Firmware
Brady Software Updates
Safety Data Sheets
Technical Data Sheets
WEEE-RoHS Compliance
Product Certification
Printer Registration

Resources

Find a Distributor
Printer Selection Tool
Label Selection Tool
Digital Catalog
Request a Catalog



Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.

Contact
6555 W. Good Hope Rd. Milwaukee WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CST
Monday - Thursday;
Friday 7am-5pm CST

About
Corporation
Privacy Policy
Terms and Conditions
Terms of Use
ISO Certificates

Other
Brady Sites
Distributor Portal
International Sites
Safety Services & Software
Smart ID Brand Protection



© 2018 Brady Worldwide, Inc.