Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



ECX-02U Faceplates and Panels - FX ECX 2U Housing 19" width







For more Information please call

1-800-Belden1



General Description:

FiberExpress ECX Patch Panel Housing 2U, holds 4 ECX adapter frames or cassettes

Image:



Usa	age (Overall)	
	Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
	Related Parts:	FiberExpress ECX Frames, Cassettes and Housing Accessories

Physical Characteristics (Connectivity)

Capacity

Access

Front Sliding Drawer Termination Area:

Dimensions

Dimensions:

Height (mm)	Width (mm)	Depth (mm)
86.106	485.648	446.024

Materials

Materials:

Description	Material
Housing	Steel
Housing	PC/ABS
Housing	Polycarbonate

Color

Color: Black, White

Weight

2.472 kg Weight:

Included Parts

Screws (12-24); Screws (10-32); Tie Wraps; Velcro Straps; Identification Labels; Quick Installation Guides; Strain Reliefs Included Parts:

Packaging

Packaging: Individually packaged in a cardboard box.

Mechanical Characteristics (Connectivity)

Storage Temperature Range: -40°C To +70°C -10°C To +60°C **Operating Temperature Range:**

> Page 1 of 2 07-11-2017

Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



ECX-02U Faceplates and Panels - FX ECX 2U Housing 19" width

Applicable Specifications and Agency Compliance (Overall)				
Applicable Standards & Environmental Programs				
EU Directive 2002/95/EC (RoHS):	Yes			
EU RoHS Compliance Date (mm/dd/yyyy):	02/23/2009			
MII Order #39 (China RoHS):	EUP 50			
Suitability				
Suitability - Indoor:	Yes			

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For more information, please refer to our web site at http://www.belden.com. Installation Guide:PX106483.

Product Family

Part Numbers:

Description	Item Number
FX ECX Patch Panel Housing 1U	ECX-01U
FX ECX Patch Panel Housing 2U	ECX-02U
FX ECX Patch Panel Housing 4U	ECX-04U

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
ECX-02U	1 EA	18.000 LB			FX ECX 2U PATCH PANEL HOUSING

Revision Number: 0 Revision Date: 09-26-2016

© 2017 Belden, Inc All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sales belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Page 2 of 2