

- ? [About Brady](#)
- ? [ISO 9001](#)
- ? [Contact Us](#)
- ? [Request A Catalog](#)
- ? [Send Product Feedback](#)
  
- ? [Where to Buy](#)
- ? [Join Our Mailing List](#)

**PRODUCT, FACILITY, & SAFETY IDENTIFICATION SOLUTIONS**

COUNTRY/REGION

- WHAT'S NEW
- PRODUCTS BY CATEGORY
- PRODUCTS BY INDUSTRY
- SERVICES
- SUPPORT
- REGULATIONS/ COMPLIANCE
- LEAN MANUFACTURING & MAINTENANCE
- PRODUCT REGISTRATION

[Home](#)
[Products By Category](#)
[Labels](#)
[Pre-Printed Labels](#)
[Wire & Cable Markers](#)  
[Wire Marker Cards](#)
[Standard Numbers & Letters](#)
[Bradylite® Reflective Numbers & Letters](#)  
[Bradylite® Reflective Numbers & Letters](#)

## Bradylite® Reflective Numbers & Letters




Made from Engineering Grade-B997 material, our Bradylite® Reflective Numbers and Letters reflect light 100 times brighter than a plain white surface so are ideal for low light or dark areas. Labels are guaranteed to perform despite storms, snow, humidity and other tough environmental conditions. Special cold temperature adhesive can be applied at temps as low as 18°F (-27°C). To order simply substitute the character you need in place of the asterisk to complete the catalog number. Choose from 3 different sizes and 4 different color combinations. Characters available are: AZ, 0-9. Use DSH to order dash and BLNK to order blank. Standard package: 25 identical characters.

**Overview**

Specifications

**Catalog #:** 5000-5  
**Product #:** 50005  
**Description:** Bradylite® Reflective Numbers & Letters  
**Legend:** 5  
**Size:** 2 7/8"H x 1 3/4"W  
**Character Height:** 2 1/2"  
**Brady Material #:** [B-997](#)  
**Material Description:** Engineering Grade Bradylite® Reflective Sheetin  
**Safety Catalog:** [pg. 183](#)  
**QTY/UOM:** 25/Package  
**MSRP (US\$)\*:** \$24.85



For more information on this product, contact Brady Customer Service or an Authorized Brady Distributor. Brady products are sold through distribution. Click on the "Find a Distributor" button to find a distributor near you.

\*If you're not based in US, please contact your local Brady office for correct pricing.

For Distributors: [BradyDistributor.com](#) | [Bradyserve.com](#)  
 Additional Information: [Privacy](#) | [Copyright](#) | [Site Map](#)