



















COAXIAL CONNECTORS ACCESSORIES & ADAPTERS

<p>BNC FEMALE TO FEMALE</p>  <p>800-2406-03 PTFE insulated Gold plated beryllium copper center contacts. 50 OHM 500 VRMS</p>	<p>BNC MALE TO MALE</p>  <p>800-2407-03 PTFE insulated Gold plated beryllium copper Finger contacts. 50 OHM 500 VRMS</p>	<p>TYPE "N" FEMALE TO BNC MALE</p>  <p>800-2450-03 PTFE insulated Gold plated beryllium copper Male and Female contacts. 50 OHM 500 VRMS</p>
<p>BNC "T" 3 FEMALE</p>  <p>800-2408-03 PTFE insulated Gold plated beryllium copper center contacts. 50 OHM 500 VRMS</p>	<p>BNC FEMALE TO FEMALE FLANGE MOUNT</p>  <p>800-2463-03 PTFE insulated Gold plated beryllium center contacts. 50 OHM 500 VRMS</p> 	<p>BNC FEMALE TO TYPE "N" MALE</p>  <p>800-2451-03 PTFE insulated Gold plated beryllium copper center contact. 50 OHM 500 VRMS</p>
<p>BNC "T" FEMALE, MALE, FEMALE</p>  <p>800-2460-03 PTFE insulated Gold plated beryllium copper Female center and Male Outer Finger contacts. 50 OHM 500 VRMS</p>	<p>ISOLATED GROUND BNC FEMALE TO FEMALE</p>  <p>800-2464-03 PTFE insulated Gold plated beryllium copper center contacts. Outer Conductor is isolated from panel 50 OHM 500 VRMS</p> 	<p>BNC FEMALE TO UHF MALE</p>  <p>800-2452-03 Rexolite insulated Gold plated Male and Female contacts. 50 OHM 500 VRMS</p>
<p>BNC "T" MALE, FEMALE, FEMALE</p>  <p>800-2461-03 PTFE insulated Gold plated beryllium copper Female center and Male Outer Finger contacts. 50 OHM 500 VRMS</p>	<p>HERMETICALLY SEALED BNC FEMALE TO FEMALE</p>  <p>800-2465-03 PTFE insulated Silicon Rubber O Ring. Gold plated beryllium copper center contacts. 50 OHM 500 VRMS</p> 	<p>UHF FEMALE TO BNC MALE</p>  <p>800-2453-03 Rexolite insulation Gold plated Phos. Bronze Male and Female center contacts. 50 OHM 500 VRMS</p>
<p>RIGHT ANGLE BNC FEMALE TO BNC MALE</p>  <p>800-2462-03 PTFE insulated Gold plated beryllium copper Female center and Male Outer Finger contacts. 50 OHM 500 VRMS</p>	<p>TNC FEMALE TO FEMALE ADAPTER</p>  <p>800-2409-03 PTFE insulated Gold plated beryllium copper center contacts. 50 OHM 500 VRMS</p>	<p>BNC FEMALE TO TNC MALE</p>  <p>800-2454-03 PTFE insulated Gold plated beryllium copper Male and Female center contacts. 50 OHM 500 VRMS</p>

CONCORD