


[Labels](#) / [Labels by Property](#) / [Low Temperature Labels](#) /
3" Core Series Polypropylene Laboratory Labels

3" Core Series Polypropylene Laboratory Labels





Product Highlights

For Use with Printer:

BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i5100, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, THT 3" Core Printer

Label/Tape Size:

1 in H x 1.5 in W

Material Number:

B-7425

Color:

White

Minimum Service Temperature °F:

-112 °F

Material:

Polypropylene

Printer and Label Applications:

General Identification, Laboratory

Part Number:

THT-235-7425-2

ADD TO CART

1



Need a different size? Customize it!



Calculate how many labels you can print with one ribbon



Overview

Polypropylene (B-7425) material is ideal for general purpose barcode applications and withstands liquid nitrogen, autoclave and other harsh environments.

- Matte white polypropylene with acrylic adhesive is thermal transfer printable
- Perfect for laboratory identification such as vials, centrifuge tubes and test tubes
- Service temperature of -112 to 158° F (-80 to 70° C)

Specifications

Material Number	B-7425
Country of Origin	US - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
Catalog Page #	181
Dimensions	1 in H x 1.5 in W
UOM	Roll of 2000 Labels
Finish	Matte
Label/Tape Size	1 in H x 1.5 in W
Maximum Service Temperature °F	158 °F
Minimum Service Temperature °F	-112 °F
Product Number	121004
UPC	662820984016
Quantity per Roll	2000

Quantity per Row	1
Thickness	0.004 in
Unit Price	/Label
UNSPSC	55121612
Adhesive Type	Acrylic
Applications	Laboratory/Healthcare Identification
Color	White
For Use with Printer	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i5100, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, THT 3" Core Printer
Label/Media Format	Roll
Label Properties	Low Temperature Labels, Permanent Adhesive Labels
Material	Polypropylene
Material Properties	Autoclavable, Cryogenic storage
Printer and Label Applications	General Identification, Laboratory
Print Technology	Thermal Transfer
Resistance Properties	Chemical-Resistant, Cold-Resistant, High Temperature-Resistant, Low Temperature-Resistant
Shape	Rectangle
Suggested Ribbon Series	R4300, R6200, R6400

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Website Feedback](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources


[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Create Custom THT Labels](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

[About](#)
[Careers](#)
[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)

[Sites](#)
[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software](#)
[Brand Protection Solutions](#)

6555 W. Good Hope Rd.
Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CT
Monday - Thursday;
Friday 7am-5pm CT

manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2019 © Brady Worldwide, Inc.