




1530 Series Number and Letter Labels

1530 Series Number and Letter Labels



Product Highlights

Text Legend:

3

Part Number:

ADD TO CART

1



Add To Favorites

People Also
Viewed



Overview

B-946 vinyl is printed with weather resistant inks and is suited for use in outdoor applications where weatherability is a key consideration.

- Designed for permanent applications in severe indoor or outdoor environments
- High gloss, durable, flexible vinyl with a permanent cold temperature pressure sensitive acrylic adhesive
- Good chemical, oil and water resistance
- Average outdoor durability 8-10 years

Specifications

Material Number	B-946
Country of Origin	MX - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
Cards or Sheets per Pack	1
Catalog Page #	224
Character Height	1 in
Dimensions	1.5 in H x 0.875 in W
UOM	Card of 10 Labels
Finish	Gloss
Indoor or Outdoor Use	Outdoor Use
Maximum Service Temperature °F	180 °F
Minimum Service Temperature °F	-40 °F
PSPA Photoluminescence Class	Not Illuminated
Product Number	15303
UPC	754473153038
Quantity per Card or Sheet	10
Thickness	0.004 in
UNSPSC	55121721
Adhesive Type	Acrylic
Applications	General & Industrial ID, Pipe & Valve Marking, Safety & Compliance ID
Color	Black on Yellow
Label/Media Format	Die-Cut on Cards
Label Properties	Aggressive Adhesive Labels, Permanent Adhesive Labels, Standard High Quality Labels
Material	Vinyl
Printer and Label Applications	General Identification, Pipe Marker
Reflective Type	Non-Reflective
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, UV-Resistant, Weather-Resistant
Text Legend	3

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Website Feedback](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Create Custom THT Labels](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

Corporate


[About](#)
[Careers](#)
[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)

Other BradyContact Sites

[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software](#)
[Brand Protection Solutions](#)

6555 W. Good Hope Rd.
Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CT
Monday - Thursday;
Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2019 © Brady Worldwide, Inc.