


[Labels](#) / [Printer Labels and Ribbons](#) / [Portable Printer Labels](#) / [BMP21 PLUS Label Printer Cartridges](#) /

[BMP21 Series Indoor-Outdoor Vinyl Labels](#)



BMP21 Series Indoor-Outdoor Vinyl Labels

Part Number:

M21-750-595-PL

Label/Tape Size:

0.75 in W x 21 ft L

Material:

Vinyl

Tape Color:

Purple

For Use with Printer:

BMP®21 PLUS Portable Label Printer,
IDPAL™ Handheld Label Maker, LABPAL™
Handheld Label Maker

Material Number:

B-595

ADD TO CART

1



[Add To Favorites](#)

PEOPLE WHO VIEWED THIS ITEM ULTIMATELY BOUGHT



OVERVIEW

This durable, low-shrink vinyl with ultra-aggressive adhesive is ideal for labeling pipes, equipment, shelves and nearly any other industrial surface.

- Highly pliable material with high-tack permanent adhesive for rough, highly textured, dirty and harsh environment surfaces--including outdoors
- Conforms and adheres to "difficult" surfaces like painted cinder blocks, painted wood, textured plastic, paper-jacketed pipes and blow-molded cases
- Resistant to exposure to chemicals, greases and oils, salt spray, cleaners and detergents and general industrial grime
- All-in-one cartridge includes ribbon and label supply

SPECIFICATIONS

Material Number	B-595
UOM	Cartridge
Finish	Gloss
Indoor or Outdoor Use	Outdoor Use
Label/Tape Size	0.75 in W x 21 ft L
Maximum Service Temperature °F	180 °F
Minimum Service Temperature °F	-40 °F
Pre-Printed Areas on Label	Colored Write-On Area
PSPA Photoluminescence Class	Not Rated
Product Number	139734
UPC	754473930455
Ribbon Color	White
Ribbon Series	R4400
Roll Length	21 ft
Roll/Tape Size	0.75 in W x 21 ft L
Roll Width	0.75 in
Tape Color	Purple
Thickness	0.004 in
Adhesive Type	Acrylic
For Use with Printer	BMP®21 PLUS Portable Label Printer, IDPAL™ Handheld Label Maker, LABPAL™ Handheld Label Maker
Label/Media Format	Label/Media in Cartridge with Ribbon
Material	Vinyl
Print Technology	Thermal Transfer
Reflective Type	Non-Reflective
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Oil-Resistant, Water-Resistant

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)

Help

[Contact Us](#)
[Knowledge Center](#)

Resources

[Find a Distributor](#)
[Printer Selection Tool](#)

[Lockout Tagout Compliance](#)

[Arc Flash Labeling Requirements](#)

[Cable and Wire Label Options](#)

[Product and Barcode Labeling](#)

[Brand Protection Solutions](#)

[Confined Space Services](#)

[Visual Workplace Services](#)

[Hazcom GHS Services](#)

[Software Programming & Integration](#)

[Label Template & File Conversion](#)

[Printer Use & Training](#)

[Printer Preventative Maintenance](#)

[Toll and Custom Coating](#)

[Authentication & Tracking Services](#)

[Printer Drivers & Firmware](#)

[Brady Software Updates](#)

[Safety Data Sheets](#)

[Technical Data Sheets](#)

[WEEE-RoHS Compliance](#)

[Product Certification](#)

[Printer Registration](#)

[Label Selection Tool](#)

[Digital Catalog](#)

[Request a Catalog](#)

[Interactive Facility Map](#)

Corporate

[About](#)
[Careers](#)

[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)

[Use of](#)
[ISO](#)
[Certification](#)

Other

[Brady Sites](#)
[Distribution Portal](#)
[International Sites](#)

[Software](#)
[Smart ID](#)
[Brand Protection Solutions](#)

Resources

[Press Releases](#)

[Request a Catalog](#)

[Find a Distributor](#)
[Log Out](#)

Contact

6555 W. Good Hope Rd. Milwaukee, WI 53223

Phone: 888-250-3082

Hours: 7am-6pm CT

Monday - Thursday;
Friday
7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 Brady Worldwide, Inc.