




[Absorbents and Spill Containment](#) / [Absorbent SOCs, Pillows and Drum Covers](#) / [Absorbent SOCs](#) / [Oil Only Socs](#) /

[Oil Only Absorbent Sock](#)



# Oil Only Absorbent Sock

**Part Number:**

OIL806

**Absorbency Capacity:**

12 gal (US)

**Dimensions:**

3 in Dia x 8 ft L

**ADD TO CART**

1



**Add To Favorites**

**Free sample pack**  **Printable brochure** 

## PEOPLE ALSO VIEWED



## OVERVIEW

Oil Only absorbents pick up petroleum-based fluids, paints and non-water soluble chemicals while repelling water - great for indoor & outdoor use.

- Moldable SOCs wrap around machinery and conform to uneven surfaces to prevent leaks from reaching walkways
- White absorbents pick up petroleum-based fluids, paints and non-water soluble chemicals while repelling

water - great for indoor & outdoor use

- Oil Only absorbents are unaffected by temperature and impervious to rot and mildew
- Floats indefinitely even when saturated with oil

## SPECIFICATIONS

Absorbency Capacity	12 gal (US)
Absorbency Factor	9 gl/gs
Class	Oil Only
Diameter	3 in
Dimensions	3 in Dia x 8 ft L
UOM	Case
Length	8 ft
Pallet Quantity	30
Percent Recycled Content	90 %
Product Number	107746
UPC	662706132029
Color	White
Environmental Resistance Features	Fire-Resistant
Fill Material	Polypropylene
Material Texture Features	Low-Linting
Text Legend	SPC Oil Only
Type	Flexi-Sock

## SUPPORT

### — VIDEOS

[Selecting the Right Absorbent video](#)

### — LITERATURE

[SPC Oil Only Absorbents  
Safety Data Sheet](#)

## Solutions

Floor Marking Guide  
GHS Label Compliance  
Lockout Tagout Compliance  
Arc Flash Labeling Requirements  
Cable and Wire Label Options  
Product and Barcode Labeling  
Brand Protection Solutions

## Services

Lockout Tagout Services  
Arc Flash Services  
Confined Space Services  
Visual Workplace Services  
Hazcom GHS Services  
Software Programming & Integration  
Label Template & File Conversion  
Printer Use & Training  
Printer Preventative Maintenance  
Toll and Custom Coating  
Authentication & Tracking Services

## Help

Contact Us  
Knowledge Center  
Printer Drivers & Firmware  
Brady Software Updates  
Safety Data Sheets  
Technical Data Sheets  
WEEE-RoHS Compliance  
Product Certification  
Printer Registration

## Resources

Find a Distributor  
Printer Selection Tool  
Label Selection Tool  
Digital Catalog  
Request a Catalog  
Interactive Facility Map

### Corporate

About  
Careers  
Investors  
Privacy Policy  
Terms and Conditions  
Terms of Use  
ISO Certification

Brady Sites  
Distribution Portal  
International Sites  
Safety Services  
Software Smart ID and Protection Solutions

### Resources


Press Releases  
Request a Catalog  
Find a Distributor  
Log Out

### Contact

6555 W. Good Hope Rd. Milwaukee, WI 53223  
Phone: 888-250-3082  
Hours: 7am-6pm CT  
Monday - Thursday;  
Friday 7am-5pm CT

### Brady (NYSE:BRC) is a

manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 Brady Worldwide, Inc.