
Cannon VEAM BIW

SEARCH Go



Home > Search Tools > Part Number

Part Number Search

You Searched For: 110277-0000 Go

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.

ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these

Product Overview

Sales Support

Stock Check

ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.

| Our Descriptive Part Number: D110277 | |
|---|--|
| Our Global Manufacturing Part Number: 110277-0000 | |

| × | × | CONSULT FACTORY | RoHS compliant= | material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2002/95/EC |
|---|---|--------------------|-------------------|---|
| | | CONSULT FACTORY | RoHS compatible = | Compatible with lead free soldering process |

| Export Compliance | | | | |
|-------------------|-------------------------|--|--|--|
| | Country of Compliance | United States | | |
| × | Export Compliance Notes | Commercial Shipments "C" | | |
| | | Controlled by the US Department of Commerce. | | |

| Product Datasheet | |
|-----------------------|---|
| Product Group | D Subminiature Accessories |
| Where Sold | Europe, Asia Pacific, Americas |
| D Sub Accessory type | Locking Hardware |
| Application Type | Commercial |
| Shell Size | DB, DE, DC, DA |
| Material | Stainless Steel |
| D Sub Accessory Style | Spring Latch |
| Finish/Treatment | Passivated |
| Dimension A | 12,42 (.489) ±0,38 (.015) |
| Dimension B | 14,35 (.565) ±0,38 (.015) |
| Dimension C | 18,59 (.732) ±0,51 (.020) |
| Note 1 | Kit consists of 1 spring, 1 screw, 1 bracket, 1 lock washer, 1 hex nut. |
| Note 1 | Order 2 kits per connector. |
| Note 2 | Front panel mounting. |
| Nieto 2 | Spring latch assembly dimension 2,41-1,52 (.095060) does not |
| Note 3 | apply to rear panel mounting. |
| Footnote | Dimension are shown in mm (inch). Dimensions subject to change. |
| For more information | Please Contact Cannon Sales Department. |