

SAFETY - HOOK® TEST CLIP

SPECIFICATION

Safety- Hook Contact: Gold Plated Beryllium Copper

Safety- Hook Body: Polycarbonate

Wire: 20 AWG 41/36 TC PVC Jacket .087 O.D.

Banana Plug: Nickel Plated Beryllium Copper Spring in Nickel Plated Brass Body

Banana Jack: Nickel Plated Brass

Pin Tip Plug: .080 Dia. Gold Plated Brass


Handles: Molded Plastic

Alligator Clips: Plated Steel with PVC Insulator

BLK	BRN	RED	ORN	YEL	GRN	BLU	PUR	GRY	WHT
10	11	12	13	14	15	16	17	18	19

795-5000-XX SAFETY- HOOK TEST CLIP
795-5053-XX (OVERALL LENGTH = 2.5 INCHES)

COLOR



MAX. WIRE O.D.

PART NO.	"A"
795-5000-XX	.090
795-5053-XX	.144

AVAILABLE IN 10 COLORS.

795-5001-XX SAFETY- HOOK TEST CLIP KIT


COLOR



CONTAINS TWO OF PART NUMBER 795-5000.
 AVAILABLE IN 10 COLORS.
 REFER TO COLOR CHART

PATCH CORDS


SAFETY- HOOK TEST CLIP ONE END ONLY



AVAILABLE IN 10 COLORS. REFER TO COLOR CHART.

LENGTH	PART NUMBER	LENGTH	PART NUMBER
8"	795-5002-XX	36"	795-5005-XX
12"	795-5003-XX	48"	795-5006-XX
24"	795-5004-XX	60"	795-5007-XX


SAFETY- HOOK TEST CLIP TO STANDARD IN LINE BANANA JACK



AVAILABLE IN RED AND BLACK. REFER TO COLOR CHART.

LENGTH	PART NUMBER	LENGTH	PART NUMBER
12"	795-5020-XX	48"	795-5023-XX
24"	795-5021-XX	60"	795-5024-XX
36"	795-5022-XX		


SAFETY- HOOK TEST CLIP BOTH ENDS



AVAILABLE IN 10 COLORS. REFER TO COLOR CHART.

LENGTH	PART NUMBER	LENGTH	PART NUMBER
8"	795-5008-XX	36"	795-5012-XX
12"	795-5009-XX	48"	795-5013-XX
18"	795-5010-XX	60"	795-5014-XX
24"	795-5011-XX		


SAFETY- HOOK TEST CLIP TO IN LINE BANANA PLUG



AVAILABLE IN RED AND BLACK. REFER TO COLOR CHART.

LENGTH	PART NUMBER	LENGTH	PART NUMBER
12"	795-5025-XX	48"	795-5028-XX
24"	795-5026-XX	60"	795-5029-XX
36"	795-5027-XX		


SAFETY- HOOK TEST CLIP TO STANDARD STACKING BANANA PLUG



AVAILABLE IN 10 COLORS. REFER TO COLOR CHART.

LENGTH	PART NUMBER	LENGTH	PART NUMBER
12"	795-5015-XX	48"	795-5018-XX
24"	795-5016-XX	60"	795-5019-XX
36"	795-5017-XX		


SAFETY- HOOK TEST CLIP TO INSULATED MINI- ALLIGATOR CLIP



AVAILABLE IN RED AND BLACK. REFER TO COLOR CHART.

LENGTH	PART NUMBER	LENGTH	PART NUMBER
12"	795-5030-XX	48"	795-5033-XX
24"	795-5031-XX	60"	795-5034-XX
36"	795-5032-XX		


SAFETY- HOOK TEST CLIP TO MINI STACKING BANANA PLUG



AVAILABLE IN 10 COLORS. REFER TO COLOR CHART.

LENGTH	PART NUMBER	LENGTH	PART NUMBER
12"	795-5040-XX	48"	795-5043-XX
24"	795-5041-XX	60"	795-5044-XX
36"	795-5042-XX		

SAFETY- HOOK TEST CLIP TO STACKING PIN TIP PLUG



AVAILABLE IN RED AND BLACK. REFER TO COLOR CHART.

LENGTH	PART NUMBER	LENGTH	PART NUMBER
12"	795-5035-XX	48"	795-5038-XX
24"	795-5036-XX	60"	795-5039-XX
36"	795-5037-XX		



BLK	BRN	RED	ORN	YEL	GRN	BLU	PUR	GRY	WHT
10	11	12	13	14	15	16	17	18	19