


1609989 -2 Product Details

Share Print Email



1609989 -2

EMI/RFI Filters and Accessories

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Filter - EMI/RFI
- ? Filter Type = Power Line
- ? BCF (7 - 180 Amp) Series
- ? 3 Phase General Purpose Application
- ? Mount Style = Flanged

[View all Features](#)

Quick Links


- ? [Check Pricing & Availability](#)
- ? [Search for Tooling](#)
- ? [Product Feature Selector](#)
- ? [Contact Us About This Product](#)

TE Internal Number: 1609989

-2

 [Active](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? [1-1654250 -1 CORCOM EMI RFI QRG](#) (PDF, English)
- ? [1654001 Corcom Product Guide BCF Series](#) (PDF, English)

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Filter - EMI/RFI
- ? [Filter Type](#) = Power Line
- ? Series = BCF (7 - 180 Amp)
- ? [Filtered](#) = Yes

Electrical Characteristics:

- ? [Current Rating \(A\)](#) = 16
- ? [Voltage ? \(VAC\)](#) = 480
- ? Leakage Current (Line -to -Ground) Max. @ 250 VAC 50 Hz (mA) = 30

Termination Features:

- ? [Terminal Input - Output Combination](#) = Terminal Block - Terminal Block

Body Features:

- ? [Mount Style](#) = Flanged

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant
- ? Approved Standards = UL Recognized, VDE Approved

Operation/Application:

- ? [Application](#) = 3 Phase General Purpose

Other:

- ? Brand = Corcom
- ? Comment = 3 -phase applications

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

