

Confidential information. Do not forward without prior authorization.

## New V-Series Contura XIV Switch

Distributor Release

Features a sleek design with an intuitive feel provided by recessed ridges along with a center groove, which effectively defines the boundary between top and bottom switch functions.



[Download Datasheet](#) >

[Download CAD Files](#) >

[Product Training Module](#) >

[Stock Package](#) >

[Price Sheet](#) >

### Product Video



### Suggested Stock Package:

Carling Part Number: Complete Switch	List Price	10 - 99	100 - 199	200 - 499	500 - 999
V1D2BT0B-FA8C00-000	\$ 8.21	\$ 6.98	\$ 4.27	\$ 3.53	\$ 3.08
VJD2DH0B-FAAC00-000	\$ 13.68	\$ 11.63	\$ 7.11	\$ 5.88	\$ 5.13
V2D2S00B-FAZC00-000	\$ 6.02	\$ 5.12	\$ 3.13	\$ 2.59	\$ 2.26

Carling Part Number: Actuator Only	List Price	10 - 99	100 - 199	200 - 499	500 - 999
VVFA8C00-000	\$ 1.60	\$ 1.36	\$ 0.83	\$ 0.69	\$ 0.60
VVFAAC00-000	\$ 1.60	\$ 1.36	\$ 0.83	\$ 0.69	\$ 0.60
VVFAZC00-000	\$ 1.60	\$ 1.36	\$ 0.83	\$ 0.69	\$ 0.60

Carling Part Number: V-Series Removal Tool	SPECIAL OFFER
999-16702-001	\$1 each with min. order QTY of 25 pieces

[\\*Download full Stock Package](#)

### Typical Applications:

Typical Applications	NAICS	SIC
<b>On/Off Highway Equipment</b>		
Military Armored Vehicle, Tank, and Tank Components	336992	3795
Heavy Duty Truck	336120	3711
Construction Machinery	333120	3531
Farm Machinery & Equipment	333111	3523 & 3559
Mining Machinery & Equipment	333131	3532
Motor Home	336213	3716
All Other Transportation Equipment	336999	3799
<b>Marine</b>		
Boat Building	336612	3732

### Product Highlights:

- Recessed ridges and center groove define the boundary between top and bottom switch functions
- Countless options for ratings, circuits, colors, illuminations and legends
- Certified to IP66 and IP68 for front panel components
- Vibration, shock, thermoshock, moisture and salt spray resistant
- Temperature ratings from -40°C to 85°C.

### Applications:

- On/Off Highway Equipment
- Marine
- Military Armored Vehicles
- Mining Machinery and Equipment
- Any application requiring environmental protection

The V-Series Contura XIV snap-in rocker switches offer countless unique options including choices for ratings, circuits, colors, illuminations and legends. These single or double pole switches feature removable actuators in a choice of actuator styles and colors, and can be illuminated with either square or bar shaped lenses. Actuators may be purchased and stocked separately. An optional plug-in terminal connector enables pre-wiring of harnesses.

The Contura switches, with sealed option, are certified to IP66 and IP68 for front panel components, signifying complete protection against dust, prolonged spray, submersion under pressure and are recognized to UL1500 - Ignition Protection for Marine Products. These switches are vibration, shock, thermoshock, moisture and salt spray resistant with temperature ratings ranging from -40°C to 85°C.