

Two-Shot Instrument Control Knobs

Series #1221

- ▶ Control knobs and levers in thermoplastic, with or without flange and index/graduations.
- ▶ Knobs can be decorated or customized to your specific need.
- ▶ Perfect knobs for synthesizers and other electronic applications.
- ▶ A variety of shapes and diameters with plain, tapped bosses or with studs are available with standard threads to fit the application.
- ▶ A wide range of soft touch control knobs available in thermoplastic overmold.
- ▶ Colors available upon request.
- ▶ Please note: Not all variations available are listed below. Please **contact customer service** to inquire about all available options.



CHECK INVENTORY

REQUEST A QUOTE

| Item # | Diameter A | Height B | Indicator Line | Inlay | Material Type | Mounting Diameter | Mounting Type | Set Screw Thread | Color | Product Drawing |
|--------|------------|----------|----------------|-------|-------------------------|----------------------|-------------------|------------------|-------|--------------------------|
| 1221-A | 0.45 | 0.55 | Yes | No | Thermoplastic Elastomer | 0.125 | Plain Molded Hole | | BLACK | Download |
| 1221-D | 0.45 | 0.55 | Yes | No | Thermoplastic Elastomer | 0.19 | Plain Molded Hole | | BLACK | Download |
| 1221-F | 0.45 | 0.55 | Yes | No | Thermoplastic Elastomer | 0.25 | Plain Molded Hole | | BLACK | Download |
| 1221-H | 0.45 | 0.55 | Yes | No | Thermoplastic Elastomer | 0.25 | Interference Fit | | BLACK | Download |
| 1221-J | 0.45 | 0.55 | Yes | No | Thermoplastic Elastomer | M6 flattened to M4.5 | Interference Fit | | BLACK | Download |
| 1221-K | 0.45 | 0.55 | Yes | No | Thermoplastic Elastomer | 0.25 Flatted to 0.16 | Interference Fit | | BLACK | Download |
| 1221-L | 0.45 | 0.55 | Yes | No | Thermoplastic Elastomer | 6mm | Interference Fit | | BLACK | Download |

PRODUCTS

- [Knobs](#)
- [Handles](#)
- [Electronic Enclosures](#)
- [Hex Hybrid Standoffs](#)
- [Two-Shot / Soft Touch](#)
- [Frac Balls](#)
- [Cable Glands](#)
- [Rubber Grommets](#)
- [Custom Molding](#)

RESOURCES

- [Engineering Specifications](#)
- [Distributor Listing](#)
- [Sales Representative Listing](#)

COMPANY

- [About Us](#)
- [Capabilities](#)
- [Certifications](#)
- [Contact Us](#)
- [Blog](#)
- [Careers](#)

QUESTIONS ?