

Product/SKU Search

Ready to talk? Contact us ([https://vcclite.com/contact###gform\\_wrapper\\_5](https://vcclite.com/contact###gform_wrapper_5)) 1.800.522.5546



Home (<https://www.vcclite.com>) / Lamps (<https://www.vcclite.com/product-category/lamps/>) / Telephone Slide (<https://www.vcclite.com/product-category/lamps/telephone-slide/>) / LMP T-2 INC Telephone Slide Base

# LMP T-2 INC Telephone Slide Base



**SKU:** 120PSB-

**Category:** [Telephone Slide](https://www.vcclite.com/product-category/lamps/telephone-slide/)  
(<https://www.vcclite.com/product-category/lamps/telephone-slide/>)

(<https://www.vcclite.com/wp-content/uploads/2018/07/120PSB.jpg>)

## Description

## Stock Availability

## Technical Downloads

# Product Description

We use cookies to ensure that we give you the best experience on our website. Your continued use of the site constitutes your acceptance of this policy.

# Additional Information

<b>Voltage</b>	<i>120 Volts (<a href="https://www.vcclite.com/voltage/120-volts/">https://www.vcclite.com/voltage/120-volts/</a>)</i>
<b>Lamp Life</b>	<i>5,000 hours (<a href="https://www.vcclite.com/lamp-life/5000-hours/">https://www.vcclite.com/lamp-life/5000-hours/</a>)</i>
<b>Lamp Type</b>	<i>Incandescent (<a href="https://www.vcclite.com/lamp-type/incandescent/">https://www.vcclite.com/lamp-type/incandescent/</a>)</i>
<b>RoHS</b>	<i>Yes (<a href="https://www.vcclite.com/rohs/yes/">https://www.vcclite.com/rohs/yes/</a>)</i>
<b>REACH Compliant</b>	<i>Yes (<a href="https://www.vcclite.com/reach-compliant/yes/">https://www.vcclite.com/reach-compliant/yes/</a>)</i>
<b>Conflict Mineral Free</b>	<i>Yes (<a href="https://www.vcclite.com/conflict-mineral-free/yes/">https://www.vcclite.com/conflict-mineral-free/yes/</a>)</i>
<b>Rated Current</b>	<i>25mA (<a href="https://www.vcclite.com/rated-current/25ma/">https://www.vcclite.com/rated-current/25ma/</a>)</i>
<b>Lamp Base Type</b>	<i>Telephone Slide (<a href="https://www.vcclite.com/lamp-base-type/telephone-slide/">https://www.vcclite.com/lamp-base-type/telephone-slide/</a>)</i>
<b>Lamp Size</b>	<i>T-2 (<a href="https://www.vcclite.com/lamp-size/t-2/">https://www.vcclite.com/lamp-size/t-2/</a>)</i>
<b>Lamp Color</b>	<i>Clear (<a href="https://www.vcclite.com/lamp-color/clear/">https://www.vcclite.com/lamp-color/clear/</a>)</i>

**VCC** (<https://www.vcclite.com/>)    **CONTACT** (<https://www.vcclite.com/contact/>)

**CAREERS** (<https://www.vcclite.com/careers/>)

**WARRANTY POLICY** (<https://www.vcclite.com/warranty-policy/>)

**TERMS & CONDITIONS** (<https://www.vcclite.com/terms-conditions-sales/>)

**PRIVACY & SECURITY STATEMENT** (<https://www.vcclite.com/vcc-privacy-and-security-statement/>)

We use cookies to ensure that we give you the best experience on our website. Your continued use of the site constitutes your acceptance of this policy.


Ok



(<https://www.facebook.com/VisualCommunicationsCompanyLLC/?ref=bookmarks>)

 (<https://twitter.com/VCClite>)

**in** (<https://www.linkedin.com/company/visual-communications-company>)

 ([https://www.youtube.com/user/vcclite?annotation\\_id=56ddfc6a-0000-2d47-9ead-94eb2c08cb3e&feature=iv&src\\_vid=IOAL90Xvl-Y](https://www.youtube.com/user/vcclite?annotation_id=56ddfc6a-0000-2d47-9ead-94eb2c08cb3e&feature=iv&src_vid=IOAL90Xvl-Y))

 (<https://www.instagram.com/vcclite>)

© 2015, 2016, 2017, 2018 Visual Communications Company, LLC  
Contact Sales 1.800.522.5546

We use cookies to ensure that we give you the best experience on our website. Your continued use of the site constitutes your acceptance of this policy.