

IC-0075-107 IC Century Series - 107

Primary 240 x 480, 230 x 460, 220 x 440

Secondary 120/240, 115/230, 110/220
Triple Rated

VA Rating: 75.00

Weight/Lbs.: 3.7

Max Amps Primary (240/480 V): .31/.16

Max Amps Secondary (120/240 V): .63/.31

Dimensional Height A (in/mm): 2.63/67

Dimensional Width B (in/mm): 3.00/76

Dimensional Depth C (in/mm): 4.44/113

Mounting Dimension W1 (in/mm): 2.10/53.3

Mounting Dimension W2 (in/mm): 2.50/63.5

Mounting Dimension D (in/mm): 2.50/64

Dimensions and weights may change. Consult factory for Certified Drawings.

Use Connection Diagram 107 – [Click Here](#)

SKU: IC-0075-107 Category: [IC Century Series - Suffix 107](#)

Search products.

Search

PRODUCT CATEGORIES

33 & 36 Series Control Transformers

Buck-Boost Transformers

Century Series

[IC Century Series - Suffix 102](#)

[IC Century Series - Suffix 103](#)

[IC Century Series - Suffix 107](#)

[IC Century Series - Suffix 109](#)

[IC Century Series - Suffix 122](#)

DOE 2016 Compliant Energy Efficient Transformers

ES-10 CE TUV Licensed Control Transformers

ES-11 Single Phase CE Transformers

Hazardous Location - AP12

Hazardous Location - HL Series Transformers

Ignition Transformers - Magnetic and Solid State

Industrial Control

K-Factor Transformers

Lighting Disconnects

Motor Drive Isolation Transformers

Description


Features

- UL Listed, File E3210
- CUL Listed, File E3210
- CE to EN 61558 (with finger safe options installed)
- Voltage and fuse combinations suitable for global applications
 - Epoxy encapsulated copper windings
 - UL Class 105°C insulation system


- Cool operation with 55°C temperature rise
- All designs rated 50 / 60 Hertz
- DIN Rail mounting options 50 – 100 VA
- Combination screw heads for ease of installation
- IP 20 when finger safe terminal and/or fuse cover options are installed
- Meets or exceeds UL 5085, NEMA ST-1 and ANSI standards
- Jumper links provided

Single Phase General Purpose Transformers
 Three Phase ES-31 CE Approved Transformers
 Three Phase General Purpose Transformers
 Uncategorized


Related products



IC-0250-107
 IC Century Series
 - 107



IC-1000-107
 IC Century Series
 - 107



IC-0750-107
 IC Century Series
 - 107

Have Special Requirements? Contact Our Experienced Team Today!

GET QUOTE

DONGAN ELECTRIC

34760 Garfield Rd.
 Fraser MI
 48026

Toll Free +1-800.428.2626
 (USA only)
 Phone +1-313.567.8500
 (Outside US)

DOWNLOAD OUR GENERAL CATALOG



OUR OTHER FULL LINE CATALOGS

- Energy Efficient
- Century Series
- Lighting Disconnect
- Ignition
- Corporate Brochure
- Sitemap

ASSOCIATIONS

