

# IC-0100-102 IC Century Series - 102

Primary Volts Primary 120 x 240  
Secondary 24

VA Rating: 100.00

Weight/Lbs.: 4.2

Max Amps Primary (120-240V): .83/.42

Max Amps Secondary (24V): 4.17

Dimensional Height A (in/mm): 2.94/75

Dimensional Width B (in/mm): 3.38/86

Dimensional Depth C (in/mm): 4.19/106

Mounting Dimension W1 (in/mm): 2.44/62

Mounting Dimension W2 (in/mm): 2.813/71.5

Mounting Dimension D (in/mm): 2.38/60

Use Connection Diagram 102 - [Click Here](#)

SKU: IC-0100-102 Category: [IC Century Series - Suffix 102](#)

Search products.

Search

PRODUCT CATEGORIES

33 & 36 Series Control Transformers

Buck-Boost Transformers

Century Series

[IC Century Series - Suffix 102](#)

[IC Century Series - Suffix 103](#)

[IC Century Series - Suffix 107](#)

[IC Century Series - Suffix 109](#)

[IC Century Series - Suffix 122](#)

DOE 2016 Compliant Energy Efficient Transformers

ES-10 CE TUV Licensed Control Transformers

ES-11 Single Phase CE Transformers

Hazardous Location - AP12

Hazardous Location - HL Series Transformers

Ignition Transformers - Magnetic and Solid State

Industrial Control

K-Factor Transformers

Lighting Disconnects

Motor Drive Isolation Transformers

Description


Features

- UL Listed, File E3210
- CUL Listed, File E3210
- CE to EN 61558 (with finger safe options installed)
- Voltage and fuse combinations suitable for global applications
  - Epoxy encapsulated copper windings
  - UL Class 105°C insulation system
  - Cool operation with 55°C temperature rise
  - All designs rated 50 / 60 Hertz
  - DIN Rail mounting options 50 - 100 VA
  - Combination screw heads for ease of installation
  - IP 20 when finger safe terminal and/or fuse cover options are installed


- Meets or exceeds UL 5085, NEMA ST-1 and ANSI standards
- Jumper links provided

Single Phase General Purpose Transformers  
 Three Phase ES-31 CE Approved Transformers  
 Three Phase General Purpose Transformers  
 Uncategorized


## Related products



IC-0075-102  
 IC Century Series  
 - 102



IC-0350-102  
 IC Century Series  
 - 102



IC-0050-102  
 IC Century Series  
 - 102

Have Special Requirements? Contact Our Experienced Team Today!

GET QUOTE

### DONGAN ELECTRIC

34760 Garfield Rd.  
 Fraser MI  
 48026

Toll Free +1-800.428.2626  
 (USA only)  
 Phone +1-313.567.8500  
 (Outside US)

### DOWNLOAD OUR GENERAL CATALOG



### OUR OTHER FULL LINE CATALOGS

- Energy Efficient
- Century Series
- Lighting Disconnect
- Ignition
- Corporate Brochure
- Sitemap

### ASSOCIATIONS

