

POWER CORDS

Computer



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6

Power Cords

Retail Part No.	Bulk Part No.	Figure No.	Description	Length (Feet)	Color	Cable	Rating
45-400		1	AC (Male) (Molded)/AC (Female) (Shrouded)	6	Black	3 x 18 AWG Stranded	125V, 10A, 75°C
45-406		1	AC (Male) (Molded)/AC (Female) (Shrouded)	10	Black	3 x 18 AWG Stranded	125V, 10A, 75°C
45-407		2	AC (Male) (Molded)/Right Angle AC (Female) (Shrouded)	20	Black	3 x 18 AWG Stranded	125V, 10A, 75°C
45-403		3	AC (Male) (Shrouded)/AC (Female) (Shrouded)	1	Black	3 x 18 AWG Stranded	125V, 10A, 75°C
45-404		3	AC (Male) (Shrouded)/AC (Female) (Shrouded)	6	Black	3 x 18 AWG Stranded	125V, 10A, 105°C
45-412		3	AC (Male) (Shrouded)/AC (Female) (Shrouded)	12	Black	3 x 18 AWG Stranded	125V, 10A, 75°C
45-415		3	AC (Male) (Shrouded)/AC (Female) (Shrouded)	15	Black	3 x 18 AWG Stranded	125V, 10A, 75°C

Monitor Power & Adapter Cords

Retail Part No.	Bulk Part No.	Figure No.	Description	Length (Feet)	Color	Cable	Rating
45-401		4	AC (Male) (Shrouded)/AC (Female) (Molded)	1	Black	3 x 18 AWG Stranded	125V, 10A, 105°C
45-408		4	AC (Male) (Shrouded)/AC (Female) (Molded)	6	Black	3 x 18 AWG Stranded	125V, 10A, 75°C
45-409		4	AC (Male) (Shrouded)/AC (Female) (Molded)	12	Black	3 x 18 AWG Stranded	125V, 10A, 75°C

Extension Cord

Retail Part No.	Bulk Part No.	Figure No.	Description	Length (Feet)	Color	Cable	Rating
45-402		5	AC (Male) (Molded)/AC (Female) (Molded)	6	Black	3 x 16 AWG Stranded	125V, 13A, 105°C

Laptop Charger Cord IEC-320-C5

Retail Part No.	Bulk Part No.	Figure No.	Description	Length (Feet)	Color	Cable	Rating
45-418		6	AC (Male) (Molded)/AC (Female) (Molded)	6	Black	3 x 18 AWG Stranded	125V, 10A, 75°C

COOLING FANS



Fig. 7



Fig. 8




Fig. 9

Equipment Cooling Fan 115VAC

Retail Part No.	Bulk Part No.	Figure No.	Description	Color
2597		7	Standard 4-1/8", 115VAC, 60 Hz, 3100 RPM, 105 CFM airflow	Black

CPU Cooling Fans 12VDC

Retail Part No.	Bulk Part No.	Figure No.	Description	Color
45-4586		8	486 & Pentium™ Fan with Heat Sink, (2 x 2.06 x 0.875")	Black
45-4687		9	Pentium™ CPU Cooling Fan with Heatsink, (2.36 x 2.36 x 2.18")	Black