

## MONITOR/VIDEO ADAPTERS

Computer



Fig.1



Fig.2



Fig.3



Fig.4



Fig.5



Fig.6



Fig.7



Fig.8



Fig.9



Fig.10



Fig.11



Fig.12



Fig.13

### Monitor Adapters

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable
45-590	45-590-BU	1	Adapter DB9 (Female)/HD15 (Female)		Gray	
45-591	45-591-BU	2	Adapter DB9 (Female)/HD15 (Male)		Putty	
45-592	45-592-BU	3	Adapter DB9 (Male)/HD15 (Female)		Putty	
45-593	45-593-BU	4	Adapter DB9 (Male)/HD15 (Male)		Putty	
45-652		5	Adapter DB25 (Male)/HD15 (Male)		Putty	

### Monitor "Y" Adapter Cable

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable
45-569		6	HD15 (Male)/HD15 (Female) (2)	2	Putty	15 x 28 AWG

### Monitor Adapter Cables

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable
45-437		7&8	DB9 (Male)/HD15 (Male)	6	Putty	9 x 28 AWG
45-438		9&10	DB9 (Female)/HD15 (Female)	6	Putty	9 x 28 AWG

### Monitor Power and Adapter Cables

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable
45-401		11,12	Shrouded (Male)/AC Molded (Female)	1	Black	3 x 18 AWG
45-408		11,12	Shrouded (Male)/AC Molded (Female)	6	Black	3 x 18 AWG
45-409		12,11	AC Molded (Female)/Shrouded (Male)	12	Black	3 x 18 AWG

### Joystick "Y" Adapter Cable

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable
45-566		13	DB15 (Male)/DB15 (Female) (2)	6	Black	10 x 26 AWG



Fig.14

### Laptop Parallel Printer Cable

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable
45-250		14	DB25 (Male)/CEN36 (Male), Flat Ribbon Style	3	Gray	28 AWG Flat Ribbon