

## WASHERS



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6

### Flat Washers

CLAMSHELL Part No.	Quantity	POLYBAG Part No.	Quantity	BULK Part No.	Quantity	Figure No.	Description	Size	Thickness (Inches)	Diameter (Inches)	
										Inner	Outer
KFW-374	25			FW-374-C	100	1	Fiber Flat Washer	4	0.03125	0.12	0.25
KFW-375	20			FW-375-C	100	1	Fiber Flat Washer	6	0.03125	0.145	0.25
KFW-376	20			FW-376-C	100	1	Fiber Flat Washer	8	0.03125	0.1875	0.375
KFW-377	20			FW-377-C	100	1	Fiber Flat Washer	10	0.03125	0.192	0.375
KFW-378	20			FW-378-C	100	1	Fiber Flat Washer	1/4	0.03125	0.255	0.5
KFW-379	15			FW-379-C	100	1	Fiber Flat Washer	3/8	0.03125	0.375	0.625
				FW-380-C	100	1	Fiber Flat Washer	7/16	0.03125	0.44	0.75
KMW-400	50	MW-400-25P	25	MW-400-C	100	2	Steel Flat Washer	2	0.018	0.092	0.21875
KMW-401	25	MW-401-25P	25	MW-401-C	100	2	Steel Flat Washer	4	0.030	0.125	0.297
KMW-402	25	MW-402-25P	25	MW-402-C	100	2	Steel Flat Washer	6	0.049	0.156	0.375
KMW-403	50	MW-403-25P	25	MW-403-C	100	2	Steel Flat Washer	8	0.049	0.188	0.438
KMW-404	50	MW-404-25P	25	MW-404-C	100	2	Steel Flat Washer	10	0.049	0.219	0.500
				MW-408-C	100	2	Steel Flat Washer	1/4	0.065	0.281	0.625
				MW-410-C	100	2	Steel Flat Washer	3/8	0.065	0.392	0.750
KNW-874	30	NW-874-25P	25	NW-874-C	100	3	Nylon Flat Washer	2	0.032	0.09	0.25
		NW-895-25P	25			3	Nylon Flat Washer	2	0.062	0.09	0.25
		NW-892-25P	25			3	Nylon Flat Washer	4	0.032	0.115	0.25
KNW-875	30	NW-875-25P	25	NW-875-C	100	3	Nylon Flat Washer	4	0.062	0.115	0.25
		NW-893-25P	25			3	Nylon Flat Washer	6	0.032	0.14	0.3125
KNW-876	30	NW-876-25P	25	NW-876-C	100	3	Nylon Flat Washer	6	0.062	0.14	0.3125
		NW-877-25P	25	NW-877-C	100	3	Nylon Flat Washer	8	0.062	0.171	0.375
		NW-896-25P	25			3	Nylon Flat Washer	10	0.032	0.194	0.375
KNW-878	25	NW-878-25P	25	NW-878-C	100	3	Nylon Flat Washer	10	0.062	0.194	0.375

### Finishing Washers

CLAMSHELL Part No.	Quantity	POLYBAG Part No.	Quantity	BULK Part No.	Quantity	Figure No.	Description	Size	Thickness (Inches)	Diameter (Inches)	
										Inner	Outer
KNW-879	7	NW-879-25P	25	NW-879-C	100	4	Nylon Finishing Washer	6	0.100	0.143	0.437
KNW-890	6	NW-890-25P	25	NW-890-C	100	4	Nylon Finishing Washer	8	0.115	0.171	0.515
KNW-891	6	NW-891-25P	25	NW-891-C	100	4	Nylon Finishing Washer	10	0.152	0.191	0.58

### Extruded Washers

CLAMSHELL Part No.	Quantity	POLYBAG Part No.	Quantity	BULK Part No.	Quantity	Figure No.	Description	Size	Thickness (Inches)	Diameter (Inches)	
										Inner	Outer
				FW-384-C	100	5	Fiber Extruded Washer	4	0.28125	0.125	0.28125
				FW-385-C	100	5	Fiber Extruded Washer	6	0.28125	0.0938	0.3125
				FW-386-C	100	5	Fiber Extruded Washer	8	0.09375	0.171	0.375
				FW-387-C	100	5	Fiber Extruded Washer	10	0.09375	0.203	0.437
				FW-388-C	100	5	Fiber Extruded Washer	1/4	0.09375	0.256	0.5
				FW-389-C	100	5	Fiber Extruded Washer	3/8	0.09375	0.375	0.625

### Internal Tooth Washers

CLAMSHELL Part No.	Quantity	POLYBAG Part No.	Quantity	BULK Part No.	Quantity	Figure No.	Description	Size	Thickness (Inches)	Diameter (Inches)	
										Inner	Outer
KMW-428	45			MW-428-C	100	6	Zinc Plated Internal Tooth Washers	2	0.013		0.185
KMW-416	45	MW-416-25P	25	MW-416-C	100	6	Zinc Plated Internal Tooth Washers	4	0.015		0.265
KMW-417	45	MW-417-25P	25	MW-417-C	100	6	Zinc Plated Internal Tooth Washers	6	0.018		0.288
KMW-418	40	MW-418-25P	25	MW-418-C	100	6	Zinc Plated Internal Tooth Washers	8	0.02		0.336
KMW-419	40	MW-419-25P	25	MW-419-C	100	6	Zinc Plated Internal Tooth Washers	10	0.022		0.381
				MW-420-C	100	6	Zinc Plated Internal Tooth Washers	1/4	0.025		0.478
				MW-421-C	100	6	Zinc Plated Internal Tooth Washers	3/8	0.035		0.692



Fig. 1



Fig. 2



Fig. 3

### External Tooth Washers

CLAMSHELL		POLYBAG		BULK		Figure No.	Description	Size	Thickness (Inches)	Diameter (Inches)	
Part No.	Quantity	Part No.	Quantity	Part No.	Quantity					Inner	Outer
				MW-422-C	100	1	Zinc Plated External Tooth Washers	4	0.015	0.255	
				MW-423-C	100	1	Zinc Plated External Tooth Washers	6	0.02	0.317	
				MW-424-C	100	1	Zinc Plated External Tooth Washers	8	0.02	0.381	
				MW-425-C	100	1	Zinc Plated External Tooth Washers	10	0.022	0.406	
				MW-426-C	100	1	Zinc Plated External Tooth Washers	1/4	0.022	0.506	
				MW-427-C	100	1	Zinc Plated External Tooth Washers	3/8	0.035	0.695	

### Split-Lock Washers

CLAMSHELL		POLYBAG		BULK		Figure No.	Description	Size	Thickness (Inches)	Diameter (Inches)	
Part No.	Quantity	Part No.	Quantity	Part No.	Quantity					Inner	Outer
KMW-411	50	MW-411-25P	25	MW-411-C	100	2	Zinc Plated Split-lock Washers	4			
KMW-412	50	MW-412-25P	25	MW-412-C	100	2	Zinc Plated Split-lock Washers	6			
KMW-413	50			MW-413-C	100	2	Zinc Plated Split-lock Washers	8			
KMW-414	50			MW-414-C	100	2	Zinc Plated Split-lock Washers	10			
KMW-415	60			MW-415-C	100	2	Zinc Plated Split-lock Washers	1/4			

### Metric Flat Washers

POLYBAG		POLYBAG		BULK		Figure No.	Description	Size	Thickness (Inches)	Diameter (Inches)	
Part No.	Quantity	Part No.	Quantity	Part No.	Quantity					Inner	Outer
WM-200-15P	15	WM-200-25P	25			3	Nickel Plated Flat Washers (Metric)	M2			
WM-205-15P	15	WM-205-25P	25			3	Nickel Plated Flat Washers (Metric)	M2.5			
WM-302-15P	15	WM-302-25P	25			3	Nickel Plated Flat Washers (Metric)	M3.2			
WM-403-15P	15	WM-403-25P	25			3	Nickel Plated Flat Washers (Metric)	M4.3			