

Stripping/Crimping Combination Tool

NEW PRODUCT



1927A

- Easily strip both solid and stranded wires, crimp terminals, cut screws and wire.
- Precision ground blades ensure consistent stripping and cutting.
- Double dipped ergonomic grips for superior comfort and assured grip.
- Heat treated for strength with black oxide finish for rust resistance.
- Narrow, serrated nose pliers for bending, pulling, and shaping wire.
- Lock tab protects cutting edges during storage.
- Cleanly cuts #4-40, #5-40, #6-32 and #8-32, #10-24, #10-32 screws.
- Crimps 10-22 AWG insulated and non-insulated terminals, splices and lugs.
- Note: this is not an insulated tool.
- Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION	CAP. AWG
1927A	06851	Stripping/Crimping Combination Tool	10-22 solid and stranded

Crimping/Stripping Combination Tool

NEW PRODUCT



1923A

- Easily strip both solid and stranded wires, crimp terminals, cut screws and wire.
- Precision ground blades ensure consistent stripping and cutting.
- Double dipped grips for superior comfort and assured grip.
- Heat treated for strength with black oxide finish for rust resistance.
- Cleanly cuts and strips 10–22 AWG wire.
- 2 wire cutters: middle cuts copper, tip also cuts hardened wire.
- Cleanly cuts #4-40, #6-32 and #8-32, #10-24, #10-32 screws.
- Crimps 10-22 AWG insulated and non-insulated terminals, splices and lugs.
- Splices and terminates 7mm and 8mm ignition terminals.
- Note: this is not an insulated tool.
- Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION	CAP. AWG	
			SOLID	STRANDED
N 1923A	06850	Crimping/Stripping Combination Tool	8–18	10–22

Multi-Cable Cutter



1969



- Cuts solid/stranded wire, coaxial cable and multi-conductor cable.
- Heavy-duty, curved, precision ground blades for clean cuts.
- Double dipped ergonomic grips for superior comfort and assured grip.
- Heat treated for strength with black oxide finish for rust resistance.
- Anvil cutter for solid/stranded wires up to 8 AWG.
- Cuts Coaxial cable up to RG6 Quad, multi-conductor cable up to 1/2" diameter.
- Cleanly cuts #6-32 and #8-32 screws
- Note: This is not an insulated tool.
- Lifetime limited warranty.

CAT. NO.	UPC NO.	DESCRIPTION
1969	23948	Multi-Cable Cutter